

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573624

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573624  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-H  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBMH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3817.0 lumens  
Efficiency: N/A  
Efficacy: 65.4 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 58.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573624

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P573624

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79				79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73				73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67				67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62				62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	464976
5°	458218
10°	439078
15°	414707
20°	387102
25°	351410
30°	293393
35°	212547
40°	133046
45°	76046
50°	39659
55°	22211
60°	14153
65°	8372
70°	6214
75°	2753
80°	4103
85°	0



TEST NUMBER: P573624

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	348.3	9.1
10°-20°	913.6	23.9
20°-30°	1174.2	30.8
30°-40°	883.4	23.1
40°-50°	354.8	9.3
50°-60°	100.9	2.6
60°-70°	31.9	0.8
70°-80°	9.1	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2436.1	63.8
0°-40°	3319.5	87.0
0°-60°	3775.2	98.9
0°-90°	3817.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3817.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3785	
5°	3716	348
15°	3261	914
25°	2592	1174
35°	1417	883
45°	438	355
55°	104	101
65°	29	32
75°	6	9
85°	0	1
90°	0	



TEST NUMBER: P573624

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3784.8
2.5°	3761.7
5°	3715.6
7.5°	3629.2
10°	3519.7
12.5°	3387.4
15°	3260.6
17.5°	3116.5
20°	2960.9
22.5°	2794.1
25°	2592.4
27.5°	2350.3
30°	2068.2
32.5°	1751.2
35°	1417.2
37.5°	1106.0
40°	829.6
42.5°	610.6
45°	437.7
47.5°	299.7
50°	207.5
52.5°	144.1
55°	103.7
57.5°	74.9
60°	57.6
62.5°	40.3
65°	28.8
67.5°	23.1
70°	17.3
72.5°	11.5
75°	5.8
77.5°	5.8
80°	5.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)