

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573630

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573630  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBMLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4762.0 lumens  
Efficiency: N/A  
Efficacy: 81.5 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 58.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573630

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P573630

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	732133
5°	725175
10°	687166
15°	623879
20°	551296
25°	476607
30°	372564
35°	228474
40°	117265
45°	46597
50°	15137
55°	5205
60°	4472
65°	3576
70°	2191
75°	2895
80°	0
85°	0



TEST NUMBER: P573630

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	549.0	11.5
10°-20°	1366.8	28.7
20°-30°	1588.8	33.4
30°-40°	973.0	20.4
40°-50°	241.6	5.1
50°-60°	28.2	0.6
60°-70°	10.6	0.2
70°-80°	4.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3504.6	73.6
0°-40°	4477.6	94.0
0°-60°	4747.4	99.7
0°-90°	4762.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4762.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5959	
5°	5880	549
15°	4905	1367
25°	3516	1589
35°	1523	973
45°	268	242
55°	24	28
65°	12	11
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P573630

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5959.4
2.5°	5953.3
5°	5880.3
7.5°	5721.7
10°	5508.4
12.5°	5228.2
15°	4905.2
17.5°	4557.9
20°	4216.8
22.5°	3875.4
25°	3516.0
27.5°	3101.6
30°	2626.3
32.5°	2071.8
35°	1523.4
37.5°	1072.4
40°	731.2
42.5°	456.9
45°	268.2
47.5°	152.4
50°	79.2
52.5°	36.6
55°	24.3
57.5°	18.2
60°	18.2
62.5°	12.3
65°	12.3
67.5°	6.1
70°	6.1
72.5°	6.1
75°	6.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)