

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573678

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573678  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-LI  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3885.0 lumens  
Efficiency: N/A  
Efficacy: 66.5 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 58.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573678

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P573678

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1228264
5°	1105305
10°	856849
15°	620191
20°	429422
25°	313062
30°	227471
35°	134604
40°	56612
45°	17652
50°	2294
55°	1285
60°	1474
65°	1744
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573678

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	787.9	20.3
10°-20°	1348.9	34.7
20°-30°	1072.0	27.6
30°-40°	567.5	14.6
40°-50°	97.8	2.5
50°-60°	7.3	0.2
60°-70°	3.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3208.7	82.6
0°-40°	3776.2	97.2
0°-60°	3881.4	99.9
0°-90°	3885.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3885.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9998	
5°	8963	788
15°	4876	1349
25°	2310	1072
35°	898	567
45°	102	98
55°	6	7
65°	6	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573678

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9997.8
2.5°	9740.4
5°	8962.7
7.5°	7945.6
10°	6868.6
12.5°	5827.6
15°	4876.2
17.5°	3990.7
20°	3284.6
22.5°	2746.2
25°	2309.5
27.5°	1956.5
30°	1603.5
32.5°	1244.5
35°	897.5
37.5°	592.4
40°	353.0
42.5°	203.5
45°	101.6
47.5°	36.0
50°	12.0
52.5°	12.0
55°	6.0
57.5°	6.0
60°	6.0
62.5°	6.0
65°	6.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)