

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365889

Luminaire Tested: **FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365889
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 766.0 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365889

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P365889

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79199
5°	77891
10°	74219
15°	67819
20°	58161
25°	46668
30°	32716
35°	15113
40°	4851
45°	1570
50°	724
55°	649
60°	644
65°	576
70°	586
75°	664
80°	866
85°	1397



TEST NUMBER: P365889

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.6	13.3
10°-20°	253.2	33.1
20°-30°	265.9	34.7
30°-40°	118.0	15.4
40°-50°	15.2	2.0
50°-60°	4.8	0.6
60°-70°	3.4	0.4
70°-80°	2.5	0.3
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	620.7	81.0
0°-40°	738.7	96.4
0°-60°	758.7	99.0
0°-90°	766.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	766.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1106	
5°	1084	102
15°	915	253
25°	591	266
35°	173	118
45°	16	15
55°	5	5
65°	3	3
75°	2	2
85°	2	1
90°	0	



TEST NUMBER: P365889

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84

CANDELA DISTRIBUTION (FULL):

0°	
0°	1106.1
2.5°	1099.2
5°	1083.7
7.5°	1062.7
10°	1020.8
12.5°	973.7
15°	914.9
17.5°	844.4
20°	763.3
22.5°	678.0
25°	590.7
27.5°	492.7
30°	395.7
32.5°	290.9
35°	172.9
37.5°	92.1
40°	51.9
42.5°	28.5
45°	15.5
47.5°	7.9
50°	6.5
52.5°	5.8
55°	5.2
57.5°	4.8
60°	4.5
62.5°	3.8
65°	3.4
67.5°	2.8
70°	2.8
72.5°	2.4
75°	2.4
77.5°	2.1
80°	2.1
82.5°	1.7
85°	1.7
87.5°	1.0
90°	0.0

(END OF REPORT)