

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573690

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-LI**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P573690  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-LI  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWLI TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5225.0 lumens  
Efficiency: N/A  
Efficacy: 89.5 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 58.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P573690

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P573690

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	393291
5°	399973
10°	418045
15°	443706
20°	463152
25°	459134
30°	426981
35°	365268
40°	278297
45°	163247
50°	69742
55°	20541
60°	5897
65°	3488
70°	2155
75°	2848
80°	0
85°	0



TEST NUMBER: P573690

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	313.1	6.0
10°-20°	988.0	18.9
20°-30°	1541.3	29.5
30°-40°	1499.7	28.7
40°-50°	749.0	14.3
50°-60°	116.0	2.2
60°-70°	14.0	0.3
70°-80°	3.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2842.4	54.4
0°-40°	4342.0	83.1
0°-60°	5207.0	99.7
0°-90°	5225.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5225.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3201	
5°	3243	313
15°	3489	988
25°	3387	1541
35°	2436	1500
45°	940	749
55°	96	116
65°	12	14
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P573690

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3201.3
2.5°	3213.3
5°	3243.3
7.5°	3291.2
10°	3351.1
12.5°	3428.7
15°	3488.6
17.5°	3536.6
20°	3542.6
22.5°	3500.6
25°	3387.1
27.5°	3219.3
30°	3009.9
32.5°	2746.8
35°	2435.5
37.5°	2094.3
40°	1735.3
42.5°	1352.4
45°	939.6
47.5°	604.3
50°	364.9
52.5°	197.4
55°	95.9
57.5°	41.9
60°	24.0
62.5°	18.0
65°	12.0
67.5°	12.0
70°	6.0
72.5°	6.0
75°	6.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)