

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573714

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBNLI TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3939.1 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573714

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P573714

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1245329
5°	1120671
10°	868762
15°	628814
20°	435397
25°	317413
30°	230634
35°	136479
40°	57398
45°	17895
50°	2332
55°	1307
60°	1499
65°	1773
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573714

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	798.8	20.3
10°-20°	1367.6	34.7
20°-30°	1086.9	27.6
30°-40°	575.4	14.6
40°-50°	99.1	2.5
50°-60°	7.5	0.2
60°-70°	3.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3253.3	82.6
0°-40°	3828.7	97.2
0°-60°	3935.3	99.9
0°-90°	3939.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3939.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10137	
5°	9087	799
15°	4944	1368
25°	2342	1087
35°	910	575
45°	103	99
55°	6	7
65°	6	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573714

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10136.7
2.5°	9875.7
5°	9087.3
7.5°	8056.1
10°	6964.1
12.5°	5908.6
15°	4944.0
17.5°	4046.1
20°	3330.3
22.5°	2784.3
25°	2341.6
27.5°	1983.7
30°	1625.8
32.5°	1261.8
35°	910.0
37.5°	600.7
40°	357.9
42.5°	206.3
45°	103.0
47.5°	36.5
50°	12.2
52.5°	12.2
55°	6.1
57.5°	6.1
60°	6.1
62.5°	6.1
65°	6.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)