

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573720

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573720
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4473.0 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573720

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P573720

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82				82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61				61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55				55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50				50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43				43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39				39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	354199
5°	355552
10°	356632
15°	356646
20°	354692
25°	346381
30°	323751
35°	280351
40°	219006
45°	157131
50°	102080
55°	61108
60°	35750
65°	22965
70°	15266
75°	11534
80°	8631
85°	0



TEST NUMBER: P573720

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.6	6.1
10°-20°	791.1	17.7
20°-30°	1167.4	26.1
30°-40°	1152.0	25.8
40°-50°	705.0	15.8
50°-60°	270.3	6.0
60°-70°	84.5	1.9
70°-80°	24.8	0.6
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2233.1	49.9
0°-40°	3385.1	75.7
0°-60°	4360.4	97.5
0°-90°	4473.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4473.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2883	
5°	2883	275
15°	2804	791
25°	2555	1167
35°	1869	1152
45°	904	705
55°	285	270
65°	79	85
75°	24	25
85°	0	3
90°	0	



TEST NUMBER: P573720

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2883.1
2.5°	2889.2
5°	2883.1
7.5°	2877.0
10°	2858.8
12.5°	2834.5
15°	2804.1
17.5°	2767.7
20°	2713.0
22.5°	2652.5
25°	2555.3
27.5°	2433.8
30°	2282.2
32.5°	2094.1
35°	1869.3
37.5°	1620.5
40°	1365.6
42.5°	1128.9
45°	904.4
47.5°	703.9
50°	534.1
52.5°	394.6
55°	285.3
57.5°	200.2
60°	145.5
62.5°	109.4
65°	79.0
67.5°	60.8
70°	42.5
72.5°	30.4
75°	24.3
77.5°	12.2
80°	12.2
82.5°	6.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)