

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364465

Luminaire Tested: **FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR81**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364465  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR81  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.156", 1000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 792.0 lumens  
Efficiency: N/A  
Efficacy: 79.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.19  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364465

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR81

### Luminous Intensity Polar Plot





TEST NUMBER: P364465

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR81

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	76	73	72
4	91	81	74	69	89	80	73	68	78	72	68		75	71	67		73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	61		69	64	60		68	63	59	58
6	79	68	61	55	77	67	60	55	66	59	55		64	59	54		63	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58	53	49	47
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	42		51	46	41		50	45	41	40
10	62	50	43	39	61	50	43	38	49	43	38		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	29436
5°	31589
10°	34041
15°	35025
20°	34693
25°	32708
30°	29657
35°	25856
40°	21676
45°	17447
50°	13434
55°	9775
60°	6630
65°	4388
70°	2847
75°	2186
80°	1938
85°	2382



TEST NUMBER: P364465

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR81

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.9	5.4
10°-20°	132.5	16.7
20°-30°	189.3	23.9
30°-40°	184.1	23.2
40°-50°	133.2	16.8
50°-60°	71.4	9.0
60°-70°	26.9	3.4
70°-80°	8.8	1.1
80°-90°	2.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.7	46.1
0°-40°	548.8	69.3
0°-60°	753.4	95.1
0°-90°	792.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	792.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	411	
5°	440	43
15°	472	133
25°	414	189
35°	296	184
45°	172	133
55°	78	71
65°	26	27
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P364465

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR81

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	411.1
2.5°	422.9
5°	439.5
7.5°	457.4
10°	468.2
12.5°	472.8
15°	472.5
17.5°	466.0
20°	455.3
22.5°	438.0
25°	414.0
27.5°	388.1
30°	358.7
32.5°	328.5
35°	295.8
37.5°	262.8
40°	231.9
42.5°	200.3
45°	172.3
47.5°	145.0
50°	120.6
52.5°	98.0
55°	78.3
57.5°	61.4
60°	46.3
62.5°	34.8
65°	25.9
67.5°	18.7
70°	13.6
72.5°	10.4
75°	7.9
77.5°	6.1
80°	4.7
82.5°	3.6
85°	2.9
87.5°	1.4
90°	0.0

(END OF REPORT)