

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364467

Luminaire Tested: **FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364467
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 813.0 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364467

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P364467

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91249
5°	89169
10°	82202
15°	72808
20°	61643
25°	48832
30°	34320
35°	14291
40°	4907
45°	1306
50°	724
55°	674
60°	616
65°	610
70°	607
75°	692
80°	907
85°	1479



TEST NUMBER: P364467

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.0	14.1
10°-20°	272.5	33.5
20°-30°	279.7	34.4
30°-40°	118.4	14.6
40°-50°	14.6	1.8
50°-60°	4.8	0.6
60°-70°	3.6	0.4
70°-80°	2.8	0.3
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	667.2	82.1
0°-40°	785.6	96.6
0°-60°	805.0	99.0
0°-90°	813.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	813.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1274	
5°	1241	115
15°	982	272
25°	618	280
35°	164	118
45°	13	15
55°	5	5
65°	4	4
75°	2	3
85°	2	2
90°	0	



TEST NUMBER: P364467

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR84

CANDELA DISTRIBUTION (FULL):

	0°
0°	1274.4
2.5°	1266.1
5°	1240.6
7.5°	1196.8
10°	1130.6
12.5°	1060.2
15°	982.2
17.5°	898.5
20°	809.0
22.5°	713.7
25°	618.1
27.5°	519.3
30°	415.1
32.5°	292.5
35°	163.5
37.5°	93.8
40°	52.5
42.5°	27.7
45°	12.9
47.5°	7.5
50°	6.5
52.5°	5.8
55°	5.4
57.5°	5.0
60°	4.3
62.5°	4.0
65°	3.6
67.5°	3.2
70°	2.9
72.5°	2.9
75°	2.5
77.5°	2.5
80°	2.2
82.5°	2.2
85°	1.8
87.5°	1.1
90°	0.0

(END OF REPORT)