

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364468

Luminaire Tested: **FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR85
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 807.0 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364468

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR85

Luminous Intensity Polar Plot





TEST NUMBER: P364468

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | | 101 | 100 | 99 | | 98 | 97 | 96 | 94 |
| 2 | 109 | 104 | 100 | 97 | 107 | 102 | 99 | 96 | 99 | 96 | 94 | | 96 | 94 | 92 | | 94 | 92 | 90 | 89 |
| 3 | 104 | 98 | 93 | 90 | 102 | 97 | 92 | 89 | 94 | 90 | 87 | | 92 | 89 | 86 | | 89 | 87 | 85 | 83 |
| 4 | 99 | 92 | 87 | 83 | 97 | 91 | 86 | 83 | 89 | 85 | 82 | | 87 | 84 | 81 | | 85 | 82 | 80 | 78 |
| 5 | 95 | 87 | 82 | 78 | 93 | 86 | 81 | 77 | 84 | 80 | 77 | | 83 | 79 | 76 | | 81 | 78 | 75 | 74 |
| 6 | 91 | 82 | 77 | 73 | 89 | 82 | 76 | 73 | 80 | 76 | 72 | | 79 | 75 | 72 | | 78 | 74 | 71 | 70 |
| 7 | 87 | 78 | 73 | 69 | 85 | 77 | 72 | 69 | 76 | 72 | 68 | | 75 | 71 | 68 | | 74 | 70 | 68 | 66 |
| 8 | 83 | 74 | 69 | 65 | 82 | 74 | 68 | 65 | 73 | 68 | 65 | | 72 | 67 | 64 | | 71 | 67 | 64 | 63 |
| 9 | 79 | 71 | 65 | 62 | 78 | 70 | 65 | 61 | 69 | 65 | 61 | | 68 | 64 | 61 | | 68 | 64 | 61 | 60 |
| 10 | 76 | 67 | 62 | 58 | 75 | 67 | 62 | 58 | 66 | 61 | 58 | | 65 | 61 | 58 | | 65 | 61 | 58 | 57 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 90576 |
| 5° | 88515 |
| 10° | 81598 |
| 15° | 72275 |
| 20° | 61186 |
| 25° | 48477 |
| 30° | 34064 |
| 35° | 14187 |
| 40° | 4870 |
| 45° | 1296 |
| 50° | 713 |
| 55° | 674 |
| 60° | 616 |
| 65° | 610 |
| 70° | 607 |
| 75° | 692 |
| 80° | 866 |
| 85° | 1479 |



TEST NUMBER: P364468

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR85

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 114.1 | 14.1 |
| 10°-20° | 270.5 | 33.5 |
| 20°-30° | 277.7 | 34.4 |
| 30°-40° | 117.6 | 14.6 |
| 40°-50° | 14.5 | 1.8 |
| 50°-60° | 4.8 | 0.6 |
| 60°-70° | 3.5 | 0.4 |
| 70°-80° | 2.7 | 0.3 |
| 80°-90° | 1.6 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 662.3 | 82.1 |
| 0°-40° | 779.8 | 96.6 |
| 0°-60° | 799.1 | 99.0 |
| 0°-90° | 807.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 807.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1265 | |
| 5° | 1232 | 114 |
| 15° | 975 | 270 |
| 25° | 614 | 278 |
| 35° | 162 | 118 |
| 45° | 13 | 14 |
| 55° | 5 | 5 |
| 65° | 4 | 4 |
| 75° | 2 | 3 |
| 85° | 2 | 2 |
| 90° | 0 | |



TEST NUMBER: P364468

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR85

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1265.0 |
| 2.5° | 1256.8 |
| 5° | 1231.5 |
| 7.5° | 1187.9 |
| 10° | 1122.3 |
| 12.5° | 1052.4 |
| 15° | 975.0 |
| 17.5° | 891.8 |
| 20° | 803.0 |
| 22.5° | 708.5 |
| 25° | 613.6 |
| 27.5° | 515.5 |
| 30° | 412.0 |
| 32.5° | 290.4 |
| 35° | 162.3 |
| 37.5° | 93.1 |
| 40° | 52.1 |
| 42.5° | 27.5 |
| 45° | 12.8 |
| 47.5° | 7.5 |
| 50° | 6.4 |
| 52.5° | 5.7 |
| 55° | 5.4 |
| 57.5° | 5.0 |
| 60° | 4.3 |
| 62.5° | 3.9 |
| 65° | 3.6 |
| 67.5° | 3.2 |
| 70° | 2.9 |
| 72.5° | 2.9 |
| 75° | 2.5 |
| 77.5° | 2.5 |
| 80° | 2.1 |
| 82.5° | 2.1 |
| 85° | 1.8 |
| 87.5° | 1.1 |
| 90° | 0.0 |

(END OF REPORT)