

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364471

Luminaire Tested: **FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364471
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BI
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 788.1 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364471

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BI

Luminous Intensity Polar Plot





TEST NUMBER: P364471

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88299
5°	86243
10°	79272
15°	70547
20°	59754
25°	47521
30°	33410
35°	13942
40°	4814
45°	1246
50°	624
55°	587
60°	573
65°	559
70°	565
75°	747
80°	825
85°	1397



TEST NUMBER: P364471

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.1	14.1
10°-20°	263.6	33.5
20°-30°	272.0	34.5
30°-40°	115.7	14.7
40°-50°	13.9	1.8
50°-60°	4.2	0.5
60°-70°	3.3	0.4
70°-80°	2.7	0.3
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.8	82.1
0°-40°	762.5	96.8
0°-60°	780.5	99.0
0°-90°	788.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	788.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1233	
5°	1200	111
15°	952	264
25°	602	272
35°	160	116
45°	12	14
55°	5	4
65°	3	3
75°	3	3
85°	2	2
90°	0	



TEST NUMBER: P364471

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1233.2
2.5°	1225.2
5°	1199.9
7.5°	1156.1
10°	1090.3
12.5°	1025.5
15°	951.7
17.5°	868.6
20°	784.2
22.5°	696.2
25°	601.5
27.5°	503.8
30°	404.1
32.5°	286.4
35°	159.5
37.5°	91.7
40°	51.5
42.5°	26.6
45°	12.3
47.5°	6.6
50°	5.6
52.5°	5.0
55°	4.7
57.5°	4.3
60°	4.0
62.5°	3.7
65°	3.3
67.5°	3.0
70°	2.7
72.5°	2.7
75°	2.7
77.5°	2.3
80°	2.0
82.5°	2.0
85°	1.7
87.5°	1.0
90°	0.0

(END OF REPORT)