

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572100

Luminaire Tested: **FLD4C-08-D010 FEU4C-X-90-35 F4X-W-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P572100  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD4C-08-D010 FEU4C-X-90-35 F4X-W-X-H  
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 744.9 lumens  
Efficiency: N/A  
Efficacy: 75.5 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.87  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P572100

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-W-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P572100

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-W-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	58994
5°	59220
10°	59393
15°	59396
20°	59080
25°	57692
30°	53921
35°	46688
40°	36469
45°	26165
50°	17010
55°	10174
60°	5946
65°	3837
70°	2550
75°	1899
80°	1415
85°	0



TEST NUMBER: P572100

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-W-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.7	6.1
10°-20°	131.8	17.7
20°-30°	194.4	26.1
30°-40°	191.9	25.8
40°-50°	117.4	15.8
50°-60°	45.0	6.0
60°-70°	14.1	1.9
70°-80°	4.1	0.6
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	371.9	49.9
0°-40°	563.8	75.7
0°-60°	726.2	97.5
0°-90°	744.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	744.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	480	
5°	480	46
15°	467	132
25°	426	194
35°	311	192
45°	151	117
55°	48	45
65°	13	14
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P572100

CATALOG NUMBER: FLD4C-08-D010 FEU4C-X-90-35 F4X-W-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	480.2
2.5°	481.2
5°	480.2
7.5°	479.2
10°	476.1
12.5°	472.1
15°	467.0
17.5°	461.0
20°	451.9
22.5°	441.8
25°	425.6
27.5°	405.4
30°	380.1
32.5°	348.8
35°	311.3
37.5°	269.9
40°	227.4
42.5°	188.0
45°	150.6
47.5°	117.2
50°	89.0
52.5°	65.7
55°	47.5
57.5°	33.3
60°	24.2
62.5°	18.2
65°	13.2
67.5°	10.1
70°	7.1
72.5°	5.1
75°	4.0
77.5°	2.0
80°	2.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)