

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365186

Luminaire Tested: **FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR82**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365186  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR82  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,  
BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.187", 1000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 580.0 lumens  
Efficiency: N/A  
Efficacy: 58.0 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.09  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365186

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR82

### Luminous Intensity Polar Plot





TEST NUMBER: P365186

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR82

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	100	108	105	102	99	101	98	96		97	95	93		93	92	90	88
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	77	72		79	75	71		77	73	70	68
4	88	78	71	65	86	77	70	64	74	68	64		72	67	63		70	66	62	60
5	82	71	63	58	80	70	63	57	68	62	57		66	61	56		64	59	56	54
6	77	65	57	52	75	64	57	51	62	56	51		61	55	50		59	54	50	48
7	72	60	52	46	70	59	52	46	57	51	46		56	50	46		55	50	45	44
8	67	55	47	42	66	54	47	42	53	47	42		52	46	42		51	46	41	40
9	63	51	44	39	62	51	43	39	49	43	38		48	42	38		47	42	38	36
10	60	48	40	36	58	47	40	36	46	40	35		45	39	35		44	39	35	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	25175
5°	24732
10°	23971
15°	23135
20°	22051
25°	20620
30°	18933
35°	16966
40°	14918
45°	12708
50°	10616
55°	8701
60°	7318
65°	6218
70°	5422
75°	4565
80°	3711
85°	2958



TEST NUMBER: P365186

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR82

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	32.4	5.6
10°-20°	87.5	15.1
20°-30°	119.5	20.6
30°-40°	121.1	20.9
40°-50°	97.2	16.8
50°-60°	63.3	10.9
60°-70°	37.0	6.4
70°-80°	17.8	3.1
80°-90°	4.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.4	41.3
0°-40°	360.6	62.2
0°-60°	521.0	89.8
0°-90°	580.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	580.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	352	
5°	344	32
15°	312	88
25°	261	120
35°	194	121
45°	126	97
55°	70	63
65°	37	37
75°	16	18
85°	4	4
90°	0	



TEST NUMBER: P365186

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR82

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	351.6
2.5°	350.2
5°	344.1
7.5°	337.6
10°	329.7
12.5°	320.7
15°	312.1
17.5°	300.6
20°	289.4
22.5°	275.4
25°	261.0
27.5°	244.5
30°	229.0
32.5°	211.4
35°	194.1
37.5°	176.9
40°	159.6
42.5°	142.7
45°	125.5
47.5°	109.7
50°	95.3
52.5°	81.3
55°	69.7
57.5°	59.7
60°	51.1
62.5°	43.5
65°	36.7
67.5°	30.9
70°	25.9
72.5°	20.9
75°	16.5
77.5°	12.6
80°	9.0
82.5°	6.1
85°	3.6
87.5°	1.4
90°	0.0

(END OF REPORT)