

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P236136

Luminaire Tested: **FLD6B60D010 EU6B6/78040 F6LBM1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P236136
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6B60D010 EU6B6/78040 F6LBM1LI
Description: FAILSAFE 6 INCH RECESSED LED DOWNLIGHT
6" LED Sealed Medical, Medium (50° Beam), Specular Clear
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5535.0 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P236136

CATALOG NUMBER: FLD6B60D010 EU6B6/78040 F6LBM1LI

Luminous Intensity Polar Plot





TEST NUMBER: P236136

CATALOG NUMBER: FLD6B60D010 EU6B6/78040 F6LBM1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 101 | | 100 | 99 | 98 | | 97 | 96 | 95 | 93 |
| 2 | 107 | 102 | 98 | 94 | 105 | 100 | 97 | 93 | 97 | 94 | 91 | | 94 | 92 | 89 | | 91 | 89 | 87 | 86 |
| 3 | 102 | 95 | 90 | 85 | 100 | 93 | 89 | 85 | 91 | 87 | 83 | | 88 | 85 | 82 | | 86 | 83 | 81 | 79 |
| 4 | 96 | 88 | 82 | 78 | 94 | 87 | 82 | 77 | 85 | 80 | 77 | | 83 | 79 | 76 | | 81 | 78 | 75 | 73 |
| 5 | 91 | 82 | 76 | 72 | 89 | 81 | 76 | 71 | 79 | 74 | 71 | | 78 | 73 | 70 | | 76 | 72 | 69 | 68 |
| 6 | 86 | 77 | 71 | 66 | 85 | 76 | 70 | 66 | 74 | 69 | 65 | | 73 | 68 | 65 | | 72 | 68 | 64 | 63 |
| 7 | 82 | 72 | 66 | 61 | 80 | 71 | 65 | 61 | 70 | 65 | 61 | | 69 | 64 | 60 | | 68 | 63 | 60 | 59 |
| 8 | 77 | 68 | 61 | 57 | 76 | 67 | 61 | 57 | 66 | 60 | 57 | | 65 | 60 | 56 | | 64 | 59 | 56 | 55 |
| 9 | 74 | 64 | 57 | 53 | 72 | 63 | 57 | 53 | 62 | 57 | 53 | | 61 | 56 | 53 | | 60 | 56 | 53 | 51 |
| 10 | 70 | 60 | 54 | 50 | 69 | 59 | 54 | 50 | 59 | 53 | 50 | | 58 | 53 | 49 | | 57 | 53 | 49 | 48 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 376295 |
| 5° | 371144 |
| 10° | 353958 |
| 15° | 330679 |
| 20° | 308870 |
| 25° | 280015 |
| 30° | 229044 |
| 35° | 156684 |
| 40° | 93290 |
| 45° | 50533 |
| 50° | 24958 |
| 55° | 15253 |
| 60° | 10204 |
| 65° | 6900 |
| 70° | 4273 |
| 75° | 2823 |
| 80° | 4208 |
| 85° | 0 |



TEST NUMBER: P236136

CATALOG NUMBER: FLD6B60D010 EU6B6/78040 F6LBM1LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 529.8 | 9.6 |
| 10°-20° | 1374.9 | 24.8 |
| 20°-30° | 1751.8 | 31.6 |
| 30°-40° | 1238.0 | 22.4 |
| 40°-50° | 452.0 | 8.2 |
| 50°-60° | 125.3 | 2.3 |
| 60°-70° | 45.4 | 0.8 |
| 70°-80° | 16.2 | 0.3 |
| 80°-90° | 1.5 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 3656.6 | 66.1 |
| 0°-40° | 4894.6 | 88.4 |
| 0°-60° | 5471.8 | 98.9 |
| 0°-90° | 5535.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5535.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 5768 | |
| 5° | 5667 | 530 |
| 15° | 4896 | 1375 |
| 25° | 3890 | 1752 |
| 35° | 1967 | 1238 |
| 45° | 548 | 452 |
| 55° | 134 | 125 |
| 65° | 45 | 45 |
| 75° | 11 | 16 |
| 85° | 0 | 2 |
| 90° | 0 | |



TEST NUMBER: P236136

CATALOG NUMBER: FLD6B60D010 EU6B6/78040 F6LBM1LI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 5767.8 |
| 2.5° | 5745.4 |
| 5° | 5667.2 |
| 7.5° | 5510.7 |
| 10° | 5343.0 |
| 12.5° | 5119.4 |
| 15° | 4895.9 |
| 17.5° | 4672.3 |
| 20° | 4448.8 |
| 22.5° | 4180.5 |
| 25° | 3889.9 |
| 27.5° | 3487.5 |
| 30° | 3040.4 |
| 32.5° | 2503.8 |
| 35° | 1967.3 |
| 37.5° | 1497.8 |
| 40° | 1095.4 |
| 42.5° | 793.6 |
| 45° | 547.7 |
| 47.5° | 368.9 |
| 50° | 245.9 |
| 52.5° | 167.7 |
| 55° | 134.1 |
| 57.5° | 100.6 |
| 60° | 78.2 |
| 62.5° | 55.9 |
| 65° | 44.7 |
| 67.5° | 33.5 |
| 70° | 22.4 |
| 72.5° | 22.4 |
| 75° | 11.2 |
| 77.5° | 11.2 |
| 80° | 11.2 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)