

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365196

Luminaire Tested: **FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL85**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365196  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL85  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 1000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 841.0 lumens  
Efficiency: N/A  
Efficacy: 84.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365196

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL85

### Luminous Intensity Polar Plot





TEST NUMBER: P365196

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL85

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  | 0   |     |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 97  |  | 98  | 96  | 94  |  | 95  | 93  | 92  | 90  |
| 2   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 88  | 93  | 89  | 86  |  | 90  | 87  | 84  |  | 87  | 84  | 82  | 80  |
| 3   | 97  | 89  | 83  | 78  | 95  | 88  | 82  | 77  | 85  | 80  | 76  |  | 82  | 78  | 75  |  | 80  | 77  | 74  | 72  |
| 4   | 91  | 82  | 75  | 69  | 89  | 80  | 74  | 69  | 78  | 73  | 68  |  | 76  | 71  | 67  |  | 74  | 70  | 67  | 65  |
| 5   | 85  | 75  | 68  | 63  | 83  | 74  | 67  | 62  | 72  | 66  | 62  |  | 70  | 65  | 61  |  | 69  | 64  | 60  | 59  |
| 6   | 80  | 69  | 62  | 57  | 78  | 68  | 62  | 57  | 67  | 61  | 56  |  | 65  | 60  | 56  |  | 64  | 59  | 55  | 54  |
| 7   | 75  | 64  | 57  | 52  | 74  | 63  | 57  | 52  | 62  | 56  | 51  |  | 61  | 55  | 51  |  | 60  | 55  | 51  | 49  |
| 8   | 71  | 60  | 53  | 48  | 70  | 59  | 52  | 48  | 58  | 52  | 47  |  | 57  | 51  | 47  |  | 56  | 51  | 47  | 45  |
| 9   | 67  | 56  | 49  | 44  | 66  | 55  | 49  | 44  | 54  | 48  | 44  |  | 53  | 48  | 44  |  | 52  | 47  | 44  | 42  |
| 10  | 64  | 52  | 46  | 41  | 62  | 52  | 45  | 41  | 51  | 45  | 41  |  | 50  | 45  | 41  |  | 49  | 44  | 41  | 39  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 18618 |
| 5°  | 18207 |
| 10° | 17266 |
| 15° | 16184 |
| 20° | 15101 |
| 25° | 13891 |
| 30° | 11900 |
| 35° | 9060  |
| 40° | 6654  |
| 45° | 5041  |
| 50° | 4131  |
| 55° | 3634  |
| 60° | 3245  |
| 65° | 2844  |
| 70° | 2428  |
| 75° | 1900  |
| 80° | 1274  |
| 85° | 564   |



TEST NUMBER: P365196

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL85

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 62.0   | 7.4       |
| 10°-20°   | 160.7  | 19.1      |
| 20°-30°   | 209.4  | 24.9      |
| 30°-40°   | 170.7  | 20.3      |
| 40°-50°   | 103.3  | 12.3      |
| 50°-60°   | 68.7   | 8.2       |
| 60°-70°   | 43.9   | 5.2       |
| 70°-80°   | 19.4   | 2.3       |
| 80°-90°   | 2.9    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 432.1  | 51.4      |
| 0°-40°    | 602.8  | 71.7      |
| 0°-60°    | 774.8  | 92.1      |
| 0°-90°    | 841.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 841.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 682 |      |
| 5°  | 664 | 62   |
| 15° | 572 | 161  |
| 25° | 461 | 209  |
| 35° | 272 | 171  |
| 45° | 130 | 103  |
| 55° | 76  | 69   |
| 65° | 44  | 44   |
| 75° | 18  | 19   |
| 85° | 2   | 3    |
| 90° | 0   |      |



TEST NUMBER: P365196

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL85

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 681.6 |
| 2.5°  | 676.4 |
| 5°    | 664.0 |
| 7.5°  | 645.3 |
| 10°   | 622.5 |
| 12.5° | 597.6 |
| 15°   | 572.3 |
| 17.5° | 547.0 |
| 20°   | 519.5 |
| 22.5° | 493.1 |
| 25°   | 460.9 |
| 27.5° | 423.5 |
| 30°   | 377.3 |
| 32.5° | 324.5 |
| 35°   | 271.7 |
| 37.5° | 224.0 |
| 40°   | 186.6 |
| 42.5° | 154.7 |
| 45°   | 130.5 |
| 47.5° | 111.5 |
| 50°   | 97.2  |
| 52.5° | 85.4  |
| 55°   | 76.3  |
| 57.5° | 67.5  |
| 60°   | 59.4  |
| 62.5° | 51.7  |
| 65°   | 44.0  |
| 67.5° | 37.0  |
| 70°   | 30.4  |
| 72.5° | 23.8  |
| 75°   | 18.0  |
| 77.5° | 12.8  |
| 80°   | 8.1   |
| 82.5° | 4.4   |
| 85°   | 1.8   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)