

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364449

Luminaire Tested: **FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BTR84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364449  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BTR84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 1000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 778.0 lumens  
Efficiency: N/A  
Efficacy: 77.8 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364449

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BTR84

### Luminous Intensity Polar Plot





TEST NUMBER: P364449

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BTR84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	87318
5°	85330
10°	78668
15°	69673
20°	58992
25°	46731
30°	32840
35°	13680
40°	4692
45°	1256
50°	691
55°	649
60°	587
65°	576
70°	586
75°	664
80°	866
85°	1397



TEST NUMBER: P364449

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BTR84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.0	14.1
10°-20°	260.8	33.5
20°-30°	267.7	34.4
30°-40°	113.4	14.6
40°-50°	13.9	1.8
50°-60°	4.6	0.6
60°-70°	3.4	0.4
70°-80°	2.7	0.3
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	638.5	82.1
0°-40°	751.8	96.6
0°-60°	770.4	99.0
0°-90°	778.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	778.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1220	
5°	1187	110
15°	940	261
25°	592	268
35°	156	113
45°	12	14
55°	5	5
65°	3	3
75°	2	3
85°	2	2
90°	0	



TEST NUMBER: P364449

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-LI-BTR84

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1219.5
2.5°	1211.6
5°	1187.2
7.5°	1145.2
10°	1082.0
12.5°	1014.6
15°	939.9
17.5°	859.8
20°	774.2
22.5°	683.0
25°	591.5
27.5°	497.0
30°	397.2
32.5°	279.9
35°	156.5
37.5°	89.8
40°	50.2
42.5°	26.5
45°	12.4
47.5°	7.2
50°	6.2
52.5°	5.5
55°	5.2
57.5°	4.8
60°	4.1
62.5°	3.8
65°	3.4
67.5°	3.1
70°	2.8
72.5°	2.8
75°	2.4
77.5°	2.4
80°	2.1
82.5°	2.1
85°	1.7
87.5°	1.0
90°	0.0

(END OF REPORT)