

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365916

Luminaire Tested: **FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BL85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365916
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BL85
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 957.0 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365916

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P365916

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33666
5°	33526
10°	31847
15°	28929
20°	25173
25°	21402
30°	16837
35°	9607
40°	4322
45°	1819
50°	574
55°	176
60°	120
65°	97
70°	88
75°	116
80°	63
85°	125



TEST NUMBER: P365916

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.4	11.9
10°-20°	284.6	29.7
20°-30°	322.5	33.7
30°-40°	186.9	19.5
40°-50°	41.5	4.3
50°-60°	4.5	0.5
60°-70°	1.5	0.2
70°-80°	1.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	721.4	75.4
0°-40°	908.3	94.9
0°-60°	954.3	99.7
0°-90°	957.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	957.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1232	
5°	1223	114
15°	1023	285
25°	710	322
35°	288	187
45°	47	41
55°	4	5
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P365916

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	1232.5
2.5°	1233.6
5°	1222.7
7.5°	1196.0
10°	1148.2
12.5°	1090.1
15°	1023.0
17.5°	952.1
20°	866.0
22.5°	788.2
25°	710.1
27.5°	626.8
30°	533.8
32.5°	423.9
35°	288.1
37.5°	185.1
40°	121.2
42.5°	79.2
45°	47.1
47.5°	26.3
50°	13.5
52.5°	6.2
55°	3.7
57.5°	2.9
60°	2.2
62.5°	1.8
65°	1.5
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.7
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)