

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365932

Luminaire Tested: **FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-11)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH
Description: VANDAL RESISTANT OPEN, WARM HAZE REFLECTOR, 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1048.0 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.84
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365932

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH

Luminous Intensity Polar Plot





TEST NUMBER: P365932

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	62	59	67	62	59	66	62	58	65	61	58	57
10	74	65	59	56	73	64	59	56	64	59	55	63	58	55	62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37807
5°	37431
10°	35556
15°	32323
20°	27964
25°	23680
30°	18483
35°	10291
40°	4507
45°	1812
50°	497
55°	86
60°	60
65°	45
70°	32
75°	42
80°	0
85°	0



TEST NUMBER: P365932

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.6	12.2
10°-20°	317.1	30.3
20°-30°	356.3	34.0
30°-40°	201.6	19.2
40°-50°	41.5	4.0
50°-60°	3.0	0.3
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	801.0	76.4
0°-40°	1002.6	95.7
0°-60°	1047.1	99.9
0°-90°	1048.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1048.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1384	
5°	1365	128
15°	1143	317
25°	786	356
35°	309	202
45°	47	42
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P365932

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1384.1
2.5°	1378.3
5°	1365.1
7.5°	1332.4
10°	1281.9
12.5°	1218.8
15°	1143.0
17.5°	1056.9
20°	962.0
22.5°	871.1
25°	785.7
27.5°	691.1
30°	586.0
32.5°	463.6
35°	308.6
37.5°	193.5
40°	126.4
42.5°	79.9
45°	46.9
47.5°	24.9
50°	11.7
52.5°	4.0
55°	1.8
57.5°	1.5
60°	1.1
62.5°	0.7
65°	0.7
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)