

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365164

Luminaire Tested: **FLD6BX10D010-FEU6B12-8027-F6LBXVM1-MW-BL89BV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365164  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-34)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-MW-BL89BV  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS ACRYLIC, CLEAR 0.125", 1000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 833.0 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365164

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-MW-BL89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P365164

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-MW-BL89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	18441
5°	18028
10°	17188
15°	16045
20°	14973
25°	13807
30°	11758
35°	8943
40°	6547
45°	4983
50°	4050
55°	3553
60°	3196
65°	2824
70°	2388
75°	1889
80°	1306
85°	533



TEST NUMBER: P365164

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-MW-BL89BV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.6	7.4
10°-20°	159.4	19.1
20°-30°	207.7	24.9
30°-40°	169.1	20.3
40°-50°	102.0	12.2
50°-60°	67.6	8.1
60°-70°	43.4	5.2
70°-80°	19.3	2.3
80°-90°	2.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.7	51.5
0°-40°	597.8	71.8
0°-60°	767.4	92.1
0°-90°	833.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	833.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	675	
5°	658	62
15°	567	159
25°	458	208
35°	268	169
45°	129	102
55°	75	68
65°	44	43
75°	18	19
85°	2	3
90°	0	



TEST NUMBER: P365164

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-MW-BL89BV

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	675.1
2.5°	671.6
5°	657.5
7.5°	641.4
10°	619.7
12.5°	593.9
15°	567.4
17.5°	541.6
20°	515.1
22.5°	488.7
25°	458.1
27.5°	420.6
30°	372.8
32.5°	322.9
35°	268.2
37.5°	222.5
40°	183.6
42.5°	153.0
45°	129.0
47.5°	110.0
50°	95.3
52.5°	84.6
55°	74.6
57.5°	66.7
60°	58.5
62.5°	50.9
65°	43.7
67.5°	36.8
70°	29.9
72.5°	23.7
75°	17.9
77.5°	12.7
80°	8.3
82.5°	4.5
85°	1.7
87.5°	0.3
90°	0.0

(END OF REPORT)