

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365244

Luminaire Tested: **FLD6BX10D010-FEU6B12-8050-F6LBXVM1-MW-BTR87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365244
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-MW-BTR87
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 660.0 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365244

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-MW-BTR87

Luminous Intensity Polar Plot





TEST NUMBER: P365244

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-MW-BTR87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	106	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	84	77	72	91	82	76	71	80	75	71		78	73	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	61
6	82	72	65	60	80	71	64	60	69	63	59		68	63	59		66	62	58	57
7	77	67	60	55	76	66	60	55	65	59	55		63	58	54		62	58	54	52
8	73	62	56	51	72	62	55	51	61	55	51		60	54	50		59	54	50	49
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45625
5°	44872
10°	42635
15°	39836
20°	36354
25°	30432
30°	22150
35°	15323
40°	11207
45°	9032
50°	7820
55°	6916
60°	6029
65°	5151
70°	4208
75°	3154
80°	2185
85°	1890



TEST NUMBER: P365244

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-MW-BTR87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.3	8.8
10°-20°	150.1	22.7
20°-30°	173.3	26.3
30°-40°	113.0	17.1
40°-50°	70.1	10.6
50°-60°	49.8	7.5
60°-70°	30.3	4.6
70°-80°	12.6	1.9
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.7	57.8
0°-40°	494.6	74.9
0°-60°	614.6	93.1
0°-90°	660.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	660.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	637	
5°	624	58
15°	537	150
25°	385	173
35°	175	113
45°	89	70
55°	55	50
65°	30	30
75°	11	13
85°	2	3
90°	0	



TEST NUMBER: P365244

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-MW-BTR87

CANDELA DISTRIBUTION (FULL):

	0°
0°	637.2
2.5°	633.8
5°	624.3
7.5°	606.5
10°	586.4
12.5°	562.5
15°	537.4
17.5°	508.6
20°	477.1
22.5°	436.5
25°	385.2
27.5°	327.9
30°	267.9
32.5°	217.8
35°	175.3
37.5°	143.8
40°	119.9
42.5°	102.1
45°	89.2
47.5°	78.6
50°	70.2
52.5°	62.6
55°	55.4
57.5°	49.0
60°	42.1
62.5°	36.1
65°	30.4
67.5°	25.0
70°	20.1
72.5°	15.6
75°	11.4
77.5°	8.0
80°	5.3
82.5°	3.4
85°	2.3
87.5°	1.1
90°	0.0

(END OF REPORT)