

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365892

Luminaire Tested: **FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR87
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 750.0 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365892

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR87

Luminous Intensity Polar Plot





TEST NUMBER: P365892

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77545
5°	76267
10°	72670
15°	66404
20°	56942
25°	45688
30°	32038
35°	14798
40°	4748
45°	1529
50°	713
55°	624
60°	630
65°	576
70°	565
75°	664
80°	825
85°	1397



TEST NUMBER: P365892

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	13.3
10°-20°	247.9	33.1
20°-30°	260.3	34.7
30°-40°	115.5	15.4
40°-50°	14.9	2.0
50°-60°	4.6	0.6
60°-70°	3.3	0.4
70°-80°	2.4	0.3
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	607.7	81.0
0°-40°	723.2	96.4
0°-60°	742.8	99.0
0°-90°	750.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	750.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1083	
5°	1061	100
15°	896	248
25°	578	260
35°	169	116
45°	15	15
55°	5	5
65°	3	3
75°	2	2
85°	2	1
90°	0	



TEST NUMBER: P365892

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR87

CANDELA DISTRIBUTION (FULL):

0°	
0°	1083.0
2.5°	1076.2
5°	1061.1
7.5°	1040.5
10°	999.5
12.5°	953.4
15°	895.8
17.5°	826.8
20°	747.3
22.5°	663.8
25°	578.3
27.5°	482.4
30°	387.5
32.5°	284.8
35°	169.3
37.5°	90.2
40°	50.8
42.5°	27.9
45°	15.1
47.5°	7.7
50°	6.4
52.5°	5.7
55°	5.0
57.5°	4.7
60°	4.4
62.5°	3.7
65°	3.4
67.5°	2.7
70°	2.7
72.5°	2.4
75°	2.4
77.5°	2.0
80°	2.0
82.5°	1.7
85°	1.7
87.5°	1.0
90°	0.0

(END OF REPORT)