

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365895

Luminaire Tested: **FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR94**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365895
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-33)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR94
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM GLASS, TEMPERED CLEAR 0.187", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 778.0 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365895

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR94

Luminous Intensity Polar Plot





TEST NUMBER: P365895

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR94

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	73	71	69
7	86	78	72	68	85	77	72	68	76	71	67		74	70	67		73	70	67	65
8	82	74	68	64	81	73	68	64	72	67	64		71	67	63		70	66	63	62
9	79	70	64	61	78	69	64	61	68	64	60		68	63	60		67	63	60	59
10	76	66	61	57	75	66	61	57	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80008
5°	79106
10°	75098
15°	68390
20°	58855
25°	47150
30°	33270
35°	15410
40°	5010
45°	1600
50°	769
55°	687
60°	644
65°	576
70°	565
75°	747
80°	866
85°	1397



TEST NUMBER: P365895

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR94

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.8	13.2
10°-20°	255.9	32.9
20°-30°	270.0	34.7
30°-40°	120.9	15.5
40°-50°	15.8	2.0
50°-60°	4.9	0.6
60°-70°	3.4	0.4
70°-80°	2.7	0.3
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.7	80.8
0°-40°	749.6	96.3
0°-60°	770.2	99.0
0°-90°	778.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	778.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1117	
5°	1101	103
15°	923	256
25°	597	270
35°	176	121
45°	16	16
55°	6	5
65°	3	3
75°	3	3
85°	2	2
90°	0	



TEST NUMBER: P365895

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8027-F6LBXVM1-WMH-BTR94

CANDELA DISTRIBUTION (FULL):

0°	
0°	1117.4
2.5°	1110.2
5°	1100.6
7.5°	1073.4
10°	1032.9
12.5°	984.4
15°	922.6
17.5°	853.9
20°	772.4
22.5°	689.6
25°	596.8
27.5°	503.0
30°	402.4
32.5°	298.3
35°	176.3
37.5°	95.9
40°	53.6
42.5°	29.9
45°	15.8
47.5°	8.2
50°	6.9
52.5°	5.8
55°	5.5
57.5°	4.8
60°	4.5
62.5°	3.8
65°	3.4
67.5°	3.1
70°	2.7
72.5°	2.7
75°	2.7
77.5°	2.4
80°	2.1
82.5°	2.1
85°	1.7
87.5°	1.0
90°	0.0

(END OF REPORT)