

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365958

Luminaire Tested: **FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR80**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-29)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR80
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM ACRYLIC, PATTERN 12 0.125", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 860.0 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365958

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR80

Luminous Intensity Polar Plot





TEST NUMBER: P365958

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR80

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	100	92	86	82	97	91	85	81	88	84	80	85	82	79	83	80	77	76
4	94	85	79	74	92	84	78	73	82	77	72	79	75	72	78	74	71	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	79	68	61	57	77	67	61	57	66	60	56	65	60	56	64	59	56	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47
10	67	56	50	46	66	56	50	46	55	49	45	54	49	45	53	49	45	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61291
5°	60030
10°	56747
15°	51867
20°	45566
25°	38728
30°	31682
35°	24938
40°	18582
45°	13174
50°	9301
55°	6679
60°	4783
65°	3473
70°	2701
75°	2213
80°	1897
85°	1890



TEST NUMBER: P365958

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR80

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	9.1
10°-20°	194.7	22.6
20°-30°	223.9	26.0
30°-40°	178.7	20.8
40°-50°	103.0	12.0
50°-60°	49.1	5.7
60°-70°	21.3	2.5
70°-80°	8.7	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	496.6	57.8
0°-40°	675.3	78.5
0°-60°	827.4	96.2
0°-90°	860.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	860.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	856	
5°	835	78
15°	700	195
25°	490	224
35°	285	179
45°	130	103
55°	54	49
65°	20	21
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P365958

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR80

CANDELA DISTRIBUTION (FULL):

0°	
0°	856.0
2.5°	850.7
5°	835.2
7.5°	812.0
10°	780.5
12.5°	743.7
15°	699.7
17.5°	651.9
20°	598.0
22.5°	543.7
25°	490.2
27.5°	436.0
30°	383.2
32.5°	335.0
35°	285.3
37.5°	240.9
40°	198.8
42.5°	162.8
45°	130.1
47.5°	104.3
50°	83.5
52.5°	66.8
55°	53.5
57.5°	42.1
60°	33.4
62.5°	26.2
65°	20.5
67.5°	16.3
70°	12.9
72.5°	10.2
75°	8.0
77.5°	6.1
80°	4.6
82.5°	3.4
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)