

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365965

Luminaire Tested: **FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BI
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 816.1 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365965

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BI

Luminous Intensity Polar Plot





TEST NUMBER: P365965

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84526
5°	83383
10°	79374
15°	72156
20°	62131
25°	49670
30°	34824
35°	16197
40°	5122
45°	1600
50°	702
55°	662
60°	601
65°	542
70°	586
75°	692
80°	866
85°	1479



TEST NUMBER: P365965

CATALOG NUMBER: FLD6BX10D010-FEUG6B12-8050-F6LBXVM1-WMH-BTR89BI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.6	13.3
10°-20°	269.9	33.1
20°-30°	283.7	34.8
30°-40°	125.9	15.4
40°-50°	15.7	1.9
50°-60°	4.7	0.6
60°-70°	3.3	0.4
70°-80°	2.6	0.3
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	662.2	81.2
0°-40°	788.1	96.6
0°-60°	808.5	99.1
0°-90°	816.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	816.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1180	
5°	1160	109
15°	973	270
25°	629	284
35°	185	126
45°	16	16
55°	5	5
65°	3	3
75°	2	3
85°	2	2
90°	0	



TEST NUMBER: P365965

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1180.5
2.5°	1172.8
5°	1160.1
7.5°	1134.1
10°	1091.7
12.5°	1039.7
15°	973.4
17.5°	898.6
20°	815.4
22.5°	725.2
25°	628.7
27.5°	526.2
30°	421.2
32.5°	309.9
35°	185.3
37.5°	98.6
40°	54.8
42.5°	29.8
45°	15.8
47.5°	7.7
50°	6.3
52.5°	5.6
55°	5.3
57.5°	4.9
60°	4.2
62.5°	3.9
65°	3.2
67.5°	2.8
70°	2.8
72.5°	2.5
75°	2.5
77.5°	2.5
80°	2.1
82.5°	1.8
85°	1.8
87.5°	1.1
90°	0.0

(END OF REPORT)