

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365966

Luminaire Tested: **FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365966  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BV  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM ACRYLIC, CLEAR 0.125", 1000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 882.0 lumens  
Efficiency: N/A  
Efficacy: 88.2 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365966

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P365966

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 94  |
| 2   | 109 | 104 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 96  | 94  | 96  | 94  | 92  | 93  | 92  | 90  | 88  |
| 3   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 89  | 94  | 90  | 87  | 91  | 88  | 86  | 89  | 87  | 85  | 83  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 82  | 89  | 85  | 81  | 87  | 83  | 80  | 85  | 82  | 80  | 78  |
| 5   | 94  | 87  | 81  | 77  | 93  | 86  | 81  | 77  | 84  | 80  | 76  | 82  | 79  | 76  | 81  | 78  | 75  | 74  |
| 6   | 90  | 82  | 76  | 72  | 89  | 81  | 76  | 72  | 80  | 75  | 72  | 78  | 74  | 71  | 77  | 74  | 71  | 69  |
| 7   | 86  | 78  | 72  | 68  | 85  | 77  | 72  | 68  | 76  | 71  | 68  | 75  | 70  | 67  | 74  | 70  | 67  | 66  |
| 8   | 82  | 74  | 68  | 64  | 81  | 73  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 64  | 70  | 66  | 63  | 62  |
| 9   | 79  | 70  | 65  | 61  | 78  | 70  | 64  | 61  | 69  | 64  | 61  | 68  | 63  | 60  | 67  | 63  | 60  | 59  |
| 10  | 76  | 67  | 61  | 58  | 75  | 66  | 61  | 58  | 65  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 91364 |
| 5°  | 90125 |
| 10° | 85794 |
| 15° | 77990 |
| 20° | 67160 |
| 25° | 53683 |
| 30° | 37644 |
| 35° | 17508 |
| 40° | 5533  |
| 45° | 1732  |
| 50° | 757   |
| 55° | 712   |
| 60° | 659   |
| 65° | 576   |
| 70° | 628   |
| 75° | 747   |
| 80° | 948   |
| 85° | 1561  |



TEST NUMBER: P365966

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BV

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 117.4  | 13.3      |
| 10°-20°   | 291.7  | 33.1      |
| 20°-30°   | 306.7  | 34.8      |
| 30°-40°   | 136.1  | 15.4      |
| 40°-50°   | 17.0   | 1.9       |
| 50°-60°   | 5.1    | 0.6       |
| 60°-70°   | 3.6    | 0.4       |
| 70°-80°   | 2.8    | 0.3       |
| 80°-90°   | 1.6    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 715.8  | 81.2      |
| 0°-40°    | 851.9  | 96.6      |
| 0°-60°    | 874.0  | 99.1      |
| 0°-90°    | 882.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 882.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1276 |      |
| 5°  | 1254 | 117  |
| 15° | 1052 | 292  |
| 25° | 680  | 307  |
| 35° | 200  | 136  |
| 45° | 17   | 17   |
| 55° | 6    | 5    |
| 65° | 3    | 4    |
| 75° | 3    | 3    |
| 85° | 2    | 2    |
| 90° | 0    |      |



TEST NUMBER: P365966

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BV

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1276.0 |
| 2.5°  | 1267.6 |
| 5°    | 1253.9 |
| 7.5°  | 1225.9 |
| 10°   | 1180.0 |
| 12.5° | 1123.8 |
| 15°   | 1052.1 |
| 17.5° | 971.3  |
| 20°   | 881.4  |
| 22.5° | 783.9  |
| 25°   | 679.5  |
| 27.5° | 568.7  |
| 30°   | 455.3  |
| 32.5° | 335.0  |
| 35°   | 200.3  |
| 37.5° | 106.6  |
| 40°   | 59.2   |
| 42.5° | 32.2   |
| 45°   | 17.1   |
| 47.5° | 8.3    |
| 50°   | 6.8    |
| 52.5° | 6.1    |
| 55°   | 5.7    |
| 57.5° | 5.3    |
| 60°   | 4.6    |
| 62.5° | 4.2    |
| 65°   | 3.4    |
| 67.5° | 3.0    |
| 70°   | 3.0    |
| 72.5° | 2.7    |
| 75°   | 2.7    |
| 77.5° | 2.7    |
| 80°   | 2.3    |
| 82.5° | 1.9    |
| 85°   | 1.9    |
| 87.5° | 1.1    |
| 90°   | 0.0    |

(END OF REPORT)