

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364460

Luminaire Tested: **FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364460
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 900.0 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364460

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P364460

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71	77	73	70	76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63	70	65	62	69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59	66	62	59	66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56	63	59	56	63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34628
5°	33967
10°	31370
15°	27954
20°	23874
25°	20049
30°	15739
35°	8156
40°	3894
45°	1534
50°	404
55°	114
60°	76
65°	65
70°	56
75°	74
80°	47
85°	94



TEST NUMBER: P364460

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.9	12.8
10°-20°	274.7	30.5
20°-30°	303.3	33.7
30°-40°	166.9	18.5
40°-50°	35.3	3.9
50°-60°	3.0	0.3
60°-70°	0.9	0.1
70°-80°	0.7	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	692.9	77.0
0°-40°	859.8	95.5
0°-60°	898.1	99.8
0°-90°	900.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	900.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1268	
5°	1239	115
15°	988	275
25°	665	303
35°	245	167
45°	40	35
55°	2	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P364460

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BL87

CANDELA DISTRIBUTION (FULL):

0°	
0°	1267.7
2.5°	1267.0
5°	1238.8
7.5°	1195.4
10°	1131.0
12.5°	1066.8
15°	988.5
17.5°	908.8
20°	821.3
22.5°	744.6
25°	665.2
27.5°	588.5
30°	499.0
32.5°	380.9
35°	244.6
37.5°	164.9
40°	109.2
42.5°	68.2
45°	39.7
47.5°	20.4
50°	9.5
52.5°	4.1
55°	2.4
57.5°	1.7
60°	1.4
62.5°	1.0
65°	1.0
67.5°	0.7
70°	0.7
72.5°	1.0
75°	0.7
77.5°	0.3
80°	0.3
82.5°	0.3
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)