

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364472

Luminaire Tested: **FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR 0.125", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 852.1 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364472

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV

Luminous Intensity Polar Plot





TEST NUMBER: P364472

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	64	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95467
5°	93251
10°	85706
15°	76277
20°	64608
25°	51376
30°	36122
35°	15078
40°	5206
45°	1347
50°	679
55°	624
60°	616
65°	610
70°	607
75°	802
80°	907
85°	1479



TEST NUMBER: P364472

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.1	14.1
10°-20°	285.0	33.5
20°-30°	294.1	34.5
30°-40°	125.1	14.7
40°-50°	15.0	1.8
50°-60°	4.5	0.5
60°-70°	3.6	0.4
70°-80°	2.9	0.3
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.3	82.1
0°-40°	824.4	96.8
0°-60°	843.9	99.0
0°-90°	852.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1333	
5°	1297	120
15°	1029	285
25°	650	294
35°	172	125
45°	13	15
55°	5	5
65°	4	4
75°	3	3
85°	2	2
90°	0	



TEST NUMBER: P364472

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	1333.3
2.5°	1324.7
5°	1297.4
7.5°	1250.0
10°	1178.8
12.5°	1108.8
15°	1029.0
17.5°	939.2
20°	847.9
22.5°	752.7
25°	650.3
27.5°	544.7
30°	436.9
32.5°	309.7
35°	172.5
37.5°	99.2
40°	55.7
42.5°	28.7
45°	13.3
47.5°	7.2
50°	6.1
52.5°	5.4
55°	5.0
57.5°	4.7
60°	4.3
62.5°	4.0
65°	3.6
67.5°	3.2
70°	2.9
72.5°	2.9
75°	2.9
77.5°	2.5
80°	2.2
82.5°	2.2
85°	1.8
87.5°	1.1
90°	0.0

(END OF REPORT)