

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364530

Luminaire Tested: **FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364530
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL85
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1236.0 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364530

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P364530

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71	77	73	70	76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	62	70	65	62	69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59	66	62	59	66	62	59	57
10	74	65	60	56	73	65	60	56	64	59	56	63	59	56	63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47553
5°	46649
10°	43081
15°	38389
20°	32786
25°	27535
30°	21615
35°	11201
40°	5349
45°	2105
50°	552
55°	157
60°	104
65°	90
70°	72
75°	95
80°	79
85°	157



TEST NUMBER: P364530

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.8	12.8
10°-20°	377.3	30.5
20°-30°	416.6	33.7
30°-40°	229.2	18.5
40°-50°	48.4	3.9
50°-60°	4.1	0.3
60°-70°	1.3	0.1
70°-80°	0.9	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	951.6	77.0
0°-40°	1180.8	95.5
0°-60°	1233.4	99.8
0°-90°	1236.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1236.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1741	
5°	1701	158
15°	1358	377
25°	914	417
35°	336	229
45°	54	48
55°	3	4
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P364530

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	1740.9
2.5°	1740.0
5°	1701.3
7.5°	1641.7
10°	1553.2
12.5°	1465.1
15°	1357.5
17.5°	1248.0
20°	1127.9
22.5°	1022.6
25°	913.6
27.5°	808.3
30°	685.3
32.5°	523.2
35°	335.9
37.5°	226.4
40°	150.0
42.5°	93.6
45°	54.5
47.5°	28.0
50°	13.0
52.5°	5.6
55°	3.3
57.5°	2.3
60°	1.9
62.5°	1.4
65°	1.4
67.5°	0.9
70°	0.9
72.5°	1.4
75°	0.9
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)