

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365184

Luminaire Tested: **FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR80**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365184
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-14)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR80
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM ACRYLIC, PATTERN 12 0.125", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 623.0 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.95
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365184

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR80

Luminous Intensity Polar Plot





TEST NUMBER: P365184

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR80

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	92	88	84		89	85	82		86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		66	62	58	56
6	78	67	60	54	77	66	59	54	65	58	54		63	57	53		62	57	53	51
7	74	62	55	49	72	61	54	49	60	53	49		59	53	49		57	52	48	47
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		53	48	44	43
9	65	54	46	42	64	53	46	42	52	46	41		51	45	41		50	45	41	39
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33767
5°	33278
10°	31780
15°	29421
20°	26600
25°	23551
30°	20339
35°	17045
40°	14105
45°	11635
50°	9725
55°	8339
60°	7246
65°	6387
70°	5569
75°	4675
80°	3835
85°	2958



TEST NUMBER: P365184

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR80

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.4	7.0
10°-20°	110.9	17.8
20°-30°	136.4	21.9
30°-40°	122.3	19.6
40°-50°	89.5	14.4
50°-60°	60.5	9.7
60°-70°	37.6	6.0
70°-80°	18.2	2.9
80°-90°	4.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.6	46.7
0°-40°	412.9	66.3
0°-60°	562.9	90.4
0°-90°	623.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	623.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	472	
5°	463	43
15°	397	111
25°	298	136
35°	195	122
45°	115	89
55°	67	61
65°	38	38
75°	17	18
85°	4	4
90°	0	



TEST NUMBER: P365184

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR80

CANDELA DISTRIBUTION (FULL):

	0°
0°	471.6
2.5°	469.5
5°	463.0
7.5°	452.2
10°	437.1
12.5°	419.2
15°	396.9
17.5°	373.6
20°	349.1
22.5°	324.0
25°	298.1
27.5°	271.2
30°	246.0
32.5°	220.2
35°	195.0
37.5°	172.4
40°	150.9
42.5°	131.5
45°	114.9
47.5°	100.2
50°	87.3
52.5°	76.9
55°	66.8
57.5°	58.5
60°	50.6
62.5°	43.8
65°	37.7
67.5°	32.0
70°	26.6
72.5°	21.6
75°	16.9
77.5°	12.6
80°	9.3
82.5°	6.1
85°	3.6
87.5°	1.4
90°	0.0

(END OF REPORT)