

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364532

Luminaire Tested: **FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1170.9 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364532

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P364532

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45054
5°	44198
10°	40814
15°	36369
20°	31059
25°	26085
30°	20476
35°	10611
40°	5067
45°	1993
50°	527
55°	148
60°	98
65°	84
70°	72
75°	95
80°	63
85°	125



TEST NUMBER: P364532

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	12.8
10°-20°	357.4	30.5
20°-30°	394.7	33.7
30°-40°	217.2	18.5
40°-50°	45.9	3.9
50°-60°	3.9	0.3
60°-70°	1.2	0.1
70°-80°	0.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	901.6	77.0
0°-40°	1118.7	95.5
0°-60°	1168.5	99.8
0°-90°	1170.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1170.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1649	
5°	1612	149
15°	1286	357
25°	866	395
35°	318	217
45°	52	46
55°	3	4
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P364532

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL87

CANDELA DISTRIBUTION (FULL):

0°	
0°	1649.4
2.5°	1648.5
5°	1611.9
7.5°	1555.4
10°	1471.5
12.5°	1388.1
15°	1286.1
17.5°	1182.4
20°	1068.5
22.5°	968.8
25°	865.5
27.5°	765.8
30°	649.2
32.5°	495.7
35°	318.2
37.5°	214.5
40°	142.1
42.5°	88.7
45°	51.6
47.5°	26.5
50°	12.4
52.5°	5.3
55°	3.1
57.5°	2.2
60°	1.8
62.5°	1.3
65°	1.3
67.5°	0.9
70°	0.9
72.5°	1.3
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)