

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364543

Luminaire Tested: **FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR89BI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364543
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR89BI
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1025.1 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364543

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR89BI

Luminous Intensity Polar Plot





TEST NUMBER: P364543

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR89BI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114849
5°	112183
10°	103112
15°	91763
20°	77729
25°	61813
30°	43456
35°	18138
40°	6262
45°	1620
50°	813
55°	761
60°	745
65°	729
70°	733
75°	968
80°	1072
85°	1807



TEST NUMBER: P364543

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR89BI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.5	14.1
10°-20°	342.9	33.5
20°-30°	353.9	34.5
30°-40°	150.5	14.7
40°-50°	18.1	1.8
50°-60°	5.5	0.5
60°-70°	4.3	0.4
70°-80°	3.4	0.3
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	841.3	82.1
0°-40°	991.8	96.8
0°-60°	1015.3	99.0
0°-90°	1025.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1025.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1604	
5°	1561	144
15°	1238	343
25°	782	354
35°	208	151
45°	16	18
55°	6	5
65°	4	4
75°	4	3
85°	2	2
90°	0	



TEST NUMBER: P364543

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR89BI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1604.0
2.5°	1593.7
5°	1560.8
7.5°	1503.8
10°	1418.2
12.5°	1333.9
15°	1237.9
17.5°	1129.9
20°	1020.1
22.5°	905.5
25°	782.4
27.5°	655.3
30°	525.6
32.5°	372.6
35°	207.5
37.5°	119.3
40°	67.0
42.5°	34.6
45°	16.0
47.5°	8.6
50°	7.3
52.5°	6.5
55°	6.1
57.5°	5.6
60°	5.2
62.5°	4.8
65°	4.3
67.5°	3.9
70°	3.5
72.5°	3.5
75°	3.5
77.5°	3.0
80°	2.6
82.5°	2.6
85°	2.2
87.5°	1.3
90°	0.0

(END OF REPORT)