

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365188

Luminaire Tested: **FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365188
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR85
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 634.0 lumens
Efficiency: N/A
Efficacy: 63.4 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365188

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR85

Luminous Intensity Polar Plot





TEST NUMBER: P365188

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98 | | 99 | 97 | 95 | | 95 | 94 | 92 | 91 |
| 2 | 105 | 99 | 94 | 90 | 103 | 97 | 93 | 89 | 94 | 90 | 87 | | 91 | 88 | 85 | | 88 | 86 | 83 | 82 |
| 3 | 99 | 91 | 85 | 80 | 96 | 89 | 84 | 79 | 87 | 82 | 78 | | 84 | 80 | 77 | | 82 | 78 | 76 | 74 |
| 4 | 93 | 84 | 77 | 72 | 91 | 82 | 76 | 72 | 80 | 75 | 71 | | 78 | 73 | 70 | | 76 | 72 | 69 | 67 |
| 5 | 87 | 77 | 70 | 65 | 85 | 76 | 70 | 65 | 74 | 69 | 64 | | 73 | 68 | 64 | | 71 | 67 | 63 | 62 |
| 6 | 82 | 72 | 65 | 60 | 80 | 71 | 64 | 60 | 69 | 63 | 59 | | 68 | 63 | 59 | | 66 | 62 | 58 | 57 |
| 7 | 78 | 67 | 60 | 55 | 76 | 66 | 60 | 55 | 65 | 59 | 55 | | 64 | 58 | 54 | | 62 | 58 | 54 | 52 |
| 8 | 73 | 63 | 56 | 51 | 72 | 62 | 55 | 51 | 61 | 55 | 51 | | 60 | 54 | 51 | | 59 | 54 | 50 | 49 |
| 9 | 70 | 59 | 52 | 48 | 68 | 58 | 52 | 48 | 57 | 51 | 47 | | 56 | 51 | 47 | | 55 | 51 | 47 | 45 |
| 10 | 66 | 55 | 49 | 45 | 65 | 55 | 49 | 44 | 54 | 48 | 44 | | 53 | 48 | 44 | | 52 | 48 | 44 | 43 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 44057 |
| 5° | 43240 |
| 10° | 41072 |
| 15° | 38465 |
| 20° | 35020 |
| 25° | 29216 |
| 30° | 21182 |
| 35° | 14580 |
| 40° | 10712 |
| 45° | 8698 |
| 50° | 7564 |
| 55° | 6679 |
| 60° | 5814 |
| 65° | 4930 |
| 70° | 3978 |
| 75° | 2877 |
| 80° | 1938 |
| 85° | 2054 |



TEST NUMBER: P365188

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR85

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 56.3 | 8.9 |
| 10°-20° | 144.9 | 22.9 |
| 20°-30° | 166.3 | 26.2 |
| 30°-40° | 107.7 | 17.0 |
| 40°-50° | 67.6 | 10.7 |
| 50°-60° | 48.1 | 7.6 |
| 60°-70° | 29.0 | 4.6 |
| 70°-80° | 11.5 | 1.8 |
| 80°-90° | 2.5 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 367.5 | 58.0 |
| 0°-40° | 475.2 | 75.0 |
| 0°-60° | 590.9 | 93.2 |
| 0°-90° | 634.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 634.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 615 | |
| 5° | 602 | 56 |
| 15° | 519 | 145 |
| 25° | 370 | 166 |
| 35° | 167 | 108 |
| 45° | 86 | 68 |
| 55° | 54 | 48 |
| 65° | 29 | 29 |
| 75° | 10 | 12 |
| 85° | 2 | 2 |
| 90° | 0 | |



TEST NUMBER: P365188

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8030-F6LBXVM1-MW-BTR85

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 615.3 |
| 2.5° | 612.4 |
| 5° | 601.6 |
| 7.5° | 585.4 |
| 10° | 564.9 |
| 12.5° | 542.3 |
| 15° | 518.9 |
| 17.5° | 492.7 |
| 20° | 459.6 |
| 22.5° | 419.8 |
| 25° | 369.8 |
| 27.5° | 314.1 |
| 30° | 256.2 |
| 32.5° | 207.4 |
| 35° | 166.8 |
| 37.5° | 136.9 |
| 40° | 114.6 |
| 42.5° | 98.5 |
| 45° | 85.9 |
| 47.5° | 76.2 |
| 50° | 67.9 |
| 52.5° | 60.7 |
| 55° | 53.5 |
| 57.5° | 47.1 |
| 60° | 40.6 |
| 62.5° | 34.9 |
| 65° | 29.1 |
| 67.5° | 23.7 |
| 70° | 19.0 |
| 72.5° | 14.4 |
| 75° | 10.4 |
| 77.5° | 7.2 |
| 80° | 4.7 |
| 82.5° | 2.9 |
| 85° | 2.5 |
| 87.5° | 1.4 |
| 90° | 0.0 |

(END OF REPORT)