

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365983

Luminaire Tested: **FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BTR89BI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BTR89BI
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1005.0 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365983

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BTR89BI

Luminous Intensity Polar Plot





TEST NUMBER: P365983

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BTR89BI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104102
5°	102696
10°	97754
15°	88864
20°	76525
25°	61173
30°	42894
35°	19956
40°	6300
45°	1975
50°	869
55°	811
60°	745
65°	661
70°	733
75°	830
80°	1072
85°	1807



TEST NUMBER: P365983

CATALOG NUMBER: FLD6BX15D010-FEUG6B12-8027-F6LBXVM1-WMH-BTR89BI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.7	13.3
10°-20°	332.4	33.1
20°-30°	349.5	34.8
30°-40°	155.0	15.4
40°-50°	19.4	1.9
50°-60°	5.8	0.6
60°-70°	4.1	0.4
70°-80°	3.2	0.3
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	815.6	81.2
0°-40°	970.7	96.6
0°-60°	995.9	99.1
0°-90°	1005.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1005.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1454	
5°	1429	134
15°	1199	332
25°	774	349
35°	228	155
45°	20	19
55°	6	6
65°	4	4
75°	3	3
85°	2	2
90°	0	



TEST NUMBER: P365983

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BTR89BI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1453.9
2.5°	1444.4
5°	1428.8
7.5°	1396.8
10°	1344.5
12.5°	1280.5
15°	1198.8
17.5°	1106.7
20°	1004.3
22.5°	893.2
25°	774.3
27.5°	648.0
30°	518.8
32.5°	381.7
35°	228.3
37.5°	121.5
40°	67.4
42.5°	36.7
45°	19.5
47.5°	9.5
50°	7.8
52.5°	6.9
55°	6.5
57.5°	6.1
60°	5.2
62.5°	4.8
65°	3.9
67.5°	3.5
70°	3.5
72.5°	3.0
75°	3.0
77.5°	3.0
80°	2.6
82.5°	2.2
85°	2.2
87.5°	1.3
90°	0.0

(END OF REPORT)