

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365198

Luminaire Tested: **FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL87**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365198  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL87  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 1000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 797.0 lumens  
Efficiency: N/A  
Efficacy: 79.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365198

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL87

### Luminous Intensity Polar Plot





TEST NUMBER: P365198

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL87

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	98	89	83	78	95	88	82	77	85	80	76		83	78	75		80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68		76	71	68		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64	59	56	54
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60	55	51	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49	44	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	17760
5°	17346
10°	16467
15°	15401
20°	14412
25°	13219
30°	11279
35°	8633
40°	6276
45°	4790
50°	3880
55°	3405
60°	3027
65°	2631
70°	2228
75°	1741
80°	1148
85°	470



TEST NUMBER: P365198

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL87

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.2	7.4
10°-20°	153.1	19.2
20°-30°	199.1	25.0
30°-40°	162.3	20.4
40°-50°	98.0	12.3
50°-60°	64.3	8.1
60°-70°	40.6	5.1
70°-80°	17.8	2.2
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	411.4	51.6
0°-40°	573.7	72.0
0°-60°	736.0	92.3
0°-90°	797.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	797.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	650	
5°	633	59
15°	545	153
25°	439	199
35°	259	162
45°	124	98
55°	72	64
65°	41	41
75°	16	18
85°	2	3
90°	0	



TEST NUMBER: P365198

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BL87

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	650.2
2.5°	644.3
5°	632.6
7.5°	615.7
10°	593.7
12.5°	571.0
15°	544.6
17.5°	520.7
20°	495.8
22.5°	469.0
25°	438.6
27.5°	402.3
30°	357.6
32.5°	307.7
35°	258.9
37.5°	214.2
40°	176.0
42.5°	147.4
45°	124.0
47.5°	105.6
50°	91.3
52.5°	80.3
55°	71.5
57.5°	63.1
60°	55.4
62.5°	48.0
65°	40.7
67.5°	34.1
70°	27.9
72.5°	22.0
75°	16.5
77.5°	11.4
80°	7.3
82.5°	4.0
85°	1.5
87.5°	0.4
90°	0.0

(END OF REPORT)