

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364560

Luminaire Tested: **FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR87
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1083.0 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364560

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR87

Luminous Intensity Polar Plot





TEST NUMBER: P364560

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121551
5°	118781
10°	109503
15°	96989
20°	82118
25°	65052
30°	45713
35°	19038
40°	6534
45°	1742
50°	958
55°	899
60°	816
65°	813
70°	796
75°	941
80°	1196
85°	1972



TEST NUMBER: P364560

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.1	14.1
10°-20°	363.0	33.5
20°-30°	372.6	34.4
30°-40°	157.8	14.6
40°-50°	19.4	1.8
50°-60°	6.4	0.6
60°-70°	4.7	0.4
70°-80°	3.7	0.3
80°-90°	2.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	888.8	82.1
0°-40°	1046.6	96.6
0°-60°	1072.4	99.0
0°-90°	1083.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1083.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1698	
5°	1653	153
15°	1308	363
25°	823	373
35°	218	158
45°	17	19
55°	7	6
65°	5	5
75°	3	4
85°	2	2
90°	0	



TEST NUMBER: P364560

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR87

CANDELA DISTRIBUTION (FULL):

0°	
0°	1697.6
2.5°	1686.6
5°	1652.6
7.5°	1594.2
10°	1506.1
12.5°	1412.3
15°	1308.4
17.5°	1196.9
20°	1077.7
22.5°	950.8
25°	823.4
27.5°	691.8
30°	552.9
32.5°	389.7
35°	217.8
37.5°	125.0
40°	69.9
42.5°	36.9
45°	17.2
47.5°	10.1
50°	8.6
52.5°	7.7
55°	7.2
57.5°	6.7
60°	5.7
62.5°	5.3
65°	4.8
67.5°	4.3
70°	3.8
72.5°	3.8
75°	3.4
77.5°	3.4
80°	2.9
82.5°	2.9
85°	2.4
87.5°	1.4
90°	0.0

(END OF REPORT)