

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364562

Luminaire Tested: **FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR 0.125", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1159.0 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364562

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV

Luminous Intensity Polar Plot





TEST NUMBER: P364562

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	79
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129864
5°	126853
10°	116592
15°	103764
20°	87886
25°	69887
30°	49136
35°	20506
40°	7085
45°	1833
50°	925
55°	849
60°	845
65°	830
70°	816
75°	1079
80°	1196
85°	1972



TEST NUMBER: P364562

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.4	14.1
10°-20°	387.8	33.5
20°-30°	400.1	34.5
30°-40°	170.2	14.7
40°-50°	20.4	1.8
50°-60°	6.2	0.5
60°-70°	4.9	0.4
70°-80°	3.9	0.3
80°-90°	2.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	951.2	82.1
0°-40°	1121.4	96.8
0°-60°	1148.0	99.1
0°-90°	1159.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1159.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1814	
5°	1765	163
15°	1400	388
25°	885	400
35°	235	170
45°	18	20
55°	7	6
65°	5	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P364562

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	1813.7
2.5°	1802.0
5°	1764.9
7.5°	1700.4
10°	1603.6
12.5°	1508.3
15°	1399.8
17.5°	1277.6
20°	1153.4
22.5°	1023.9
25°	884.6
27.5°	740.9
30°	594.3
32.5°	421.3
35°	234.6
37.5°	134.9
40°	75.8
42.5°	39.1
45°	18.1
47.5°	9.8
50°	8.3
52.5°	7.3
55°	6.8
57.5°	6.4
60°	5.9
62.5°	5.4
65°	4.9
67.5°	4.4
70°	3.9
72.5°	3.9
75°	3.9
77.5°	3.4
80°	2.9
82.5°	2.9
85°	2.4
87.5°	1.5
90°	0.0

(END OF REPORT)