

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365208

Luminaire Tested: **FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR87
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 637.9 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365208

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR87

Luminous Intensity Polar Plot





TEST NUMBER: P365208

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	106	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	82	76	71	80	75	71		78	73	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	61
6	82	72	65	60	80	71	64	60	69	63	59		68	63	59		66	62	58	57
7	77	67	60	55	76	66	60	55	65	59	55		63	58	54		62	58	54	52
8	73	62	56	51	72	62	55	51	61	55	51		60	54	50		59	54	50	49
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44107
5°	43377
10°	41210
15°	38509
20°	35142
25°	29421
30°	21414
35°	14816
40°	10833
45°	8729
50°	7564
55°	6691
60°	5828
65°	4964
70°	4061
75°	3043
80°	2103
85°	1807



TEST NUMBER: P365208

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.4	8.8
10°-20°	145.1	22.7
20°-30°	167.5	26.3
30°-40°	109.2	17.1
40°-50°	67.8	10.6
50°-60°	48.1	7.5
60°-70°	29.3	4.6
70°-80°	12.1	1.9
80°-90°	2.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.0	57.8
0°-40°	478.2	75.0
0°-60°	594.1	93.1
0°-90°	637.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	637.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	616	
5°	604	56
15°	520	145
25°	372	167
35°	170	109
45°	86	68
55°	54	48
65°	29	29
75°	11	12
85°	2	2
90°	0	



TEST NUMBER: P365208

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR87

CANDELA DISTRIBUTION (FULL):

	0°
0°	616.0
2.5°	612.7
5°	603.5
7.5°	586.3
10°	566.8
12.5°	543.7
15°	519.5
17.5°	491.6
20°	461.2
22.5°	421.9
25°	372.4
27.5°	317.0
30°	259.0
32.5°	210.6
35°	169.5
37.5°	139.0
40°	115.9
42.5°	98.7
45°	86.2
47.5°	75.9
50°	67.9
52.5°	60.5
55°	53.6
57.5°	47.3
60°	40.7
62.5°	34.9
65°	29.3
67.5°	24.2
70°	19.4
72.5°	15.0
75°	11.0
77.5°	7.7
80°	5.1
82.5°	3.3
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)