

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365210

Luminaire Tested: **FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365210
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR 0.125", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 687.0 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365210

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR89BV

Luminous Intensity Polar Plot





TEST NUMBER: P365210

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	82	76	72	80	75	71		78	74	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	72	65	60	81	71	64	60	69	64	59		68	63	59		66	62	58	57
7	78	67	60	55	76	66	60	55	65	59	55		64	58	54		62	58	54	53
8	73	63	56	51	72	62	56	51	61	55	51		60	54	51		59	54	50	49
9	70	59	52	48	68	58	52	48	57	51	47		56	51	47		55	51	47	46
10	66	55	49	45	65	55	49	45	54	48	44		53	48	44		52	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47995
5°	47050
10°	44794
15°	41838
20°	38121
25°	31823
30°	22877
35°	15795
40°	11543
45°	9356
50°	8165
55°	7228
60°	6301
65°	5337
70°	4292
75°	3043
80°	2103
85°	2382



TEST NUMBER: P365210

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.3	8.9
10°-20°	157.8	23.0
20°-30°	180.4	26.3
30°-40°	116.1	16.9
40°-50°	72.8	10.6
50°-60°	51.9	7.6
60°-70°	31.5	4.6
70°-80°	12.3	1.8
80°-90°	2.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	399.6	58.2
0°-40°	515.7	75.1
0°-60°	640.4	93.2
0°-90°	687.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	687.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	670	
5°	655	61
15°	564	158
25°	403	180
35°	181	116
45°	92	73
55°	58	52
65°	32	31
75°	11	12
85°	3	3
90°	0	



TEST NUMBER: P365210

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-MW-BTR89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	670.3
2.5°	667.0
5°	654.6
7.5°	639.5
10°	616.1
12.5°	592.3
15°	564.4
17.5°	535.8
20°	500.3
22.5°	456.3
25°	402.8
27.5°	338.3
30°	276.7
32.5°	222.5
35°	180.7
37.5°	147.7
40°	123.5
42.5°	105.6
45°	92.4
47.5°	82.1
50°	73.3
52.5°	65.6
55°	57.9
57.5°	50.6
60°	44.0
62.5°	37.7
65°	31.5
67.5°	26.0
70°	20.5
72.5°	15.4
75°	11.0
77.5°	7.7
80°	5.1
82.5°	3.3
85°	2.9
87.5°	1.5
90°	0.0

(END OF REPORT)