

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365921

Luminaire Tested: **FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BL89BW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365921  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-46)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BL89BW  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS ACRYLIC OPAL SMOOTH, CLEAR 0.125", 1000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 739.0 lumens  
Efficiency: N/A  
Efficacy: 73.9 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365921

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BL89BW

### Luminous Intensity Polar Plot





TEST NUMBER: P365921

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BL89BW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	76	82	78	74	79	75	72	70
3	90	80	72	65	88	78	71	64	75	69	63	72	67	62	70	65	61	59
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	47	58	51	46	56	50	46	43
6	70	57	48	41	68	56	47	41	54	46	41	52	45	40	51	45	40	38
7	65	51	43	36	63	51	42	36	49	41	36	48	41	36	46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32	44	37	32	42	36	32	30
9	56	43	35	29	55	42	35	29	41	34	29	40	34	29	39	33	29	27
10	53	40	32	26	52	39	32	26	38	31	26	37	31	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	7214
5°	7200
10°	7173
15°	7126
20°	7081
25°	7022
30°	6920
35°	6853
40°	6764
45°	6695
50°	6599
55°	6472
60°	6283
65°	6011
70°	5614
75°	4992
80°	3980
85°	2413



TEST NUMBER: P365921

CATALOG NUMBER: FLD6BX10D010-FEUG6B12-8035-F6LBXVM1-WMH-BL89BW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	24.9	3.4
10°-20°	71.1	9.6
20°-30°	107.2	14.5
30°-40°	128.6	17.4
40°-50°	133.6	18.1
50°-60°	121.3	16.4
60°-70°	92.0	12.4
70°-80°	50.0	6.8
80°-90°	10.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.2	27.5
0°-40°	331.8	44.9
0°-60°	586.7	79.4
0°-90°	739.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	739.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	264	
5°	263	25
15°	252	71
25°	233	107
35°	206	129
45°	173	134
55°	136	121
65°	93	92
75°	47	50
85°	8	10
90°	0	



TEST NUMBER: P365921

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BL89BW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	264.1
2.5°	264.1
5°	262.6
7.5°	260.4
10°	258.6
12.5°	255.7
15°	252.0
17.5°	247.3
20°	243.6
22.5°	238.1
25°	233.0
27.5°	226.4
30°	219.4
32.5°	213.2
35°	205.5
37.5°	198.2
40°	189.7
42.5°	181.7
45°	173.3
47.5°	164.5
50°	155.3
52.5°	145.8
55°	135.9
57.5°	125.3
60°	115.0
62.5°	104.4
65°	93.0
67.5°	81.7
70°	70.3
72.5°	58.6
75°	47.3
77.5°	35.9
80°	25.3
82.5°	15.8
85°	7.7
87.5°	2.2
90°	0.0

(END OF REPORT)