

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365929

Luminaire Tested: **FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BTR89BI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BTR89BI
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 788.0 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365929

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BTR89BI

Luminous Intensity Polar Plot





TEST NUMBER: P365929

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BTR89BI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81626
5°	80522
10°	76647
15°	69680
20°	59998
25°	47963
30°	33634
35°	15646
40°	4945
45°	1549
50°	679
55°	637
60°	587
65°	525
70°	565
75°	664
80°	825
85°	1397



TEST NUMBER: P365929

CATALOG NUMBER: FLD6BX10D010-FEUG6B12-8035-F6LBXVM1-WMH-BTR89BI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.9	13.3
10°-20°	260.6	33.1
20°-30°	274.0	34.8
30°-40°	121.6	15.4
40°-50°	15.2	1.9
50°-60°	4.5	0.6
60°-70°	3.2	0.4
70°-80°	2.5	0.3
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	639.5	81.2
0°-40°	761.1	96.6
0°-60°	780.8	99.1
0°-90°	788.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	788.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1140	
5°	1120	105
15°	940	261
25°	607	274
35°	179	122
45°	15	15
55°	5	5
65°	3	3
75°	2	3
85°	2	1
90°	0	



TEST NUMBER: P365929

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8035-F6LBXVM1-WMH-BTR89BI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1140.0
2.5°	1132.5
5°	1120.3
7.5°	1095.2
10°	1054.2
12.5°	1004.0
15°	940.0
17.5°	867.8
20°	787.4
22.5°	700.3
25°	607.1
27.5°	508.1
30°	406.8
32.5°	299.3
35°	179.0
37.5°	95.3
40°	52.9
42.5°	28.8
45°	15.3
47.5°	7.5
50°	6.1
52.5°	5.4
55°	5.1
57.5°	4.7
60°	4.1
62.5°	3.7
65°	3.1
67.5°	2.7
70°	2.7
72.5°	2.4
75°	2.4
77.5°	2.4
80°	2.0
82.5°	1.7
85°	1.7
87.5°	1.0
90°	0.0

(END OF REPORT)