

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365999

Luminaire Tested: **FLD6BX15D010-FEU6B12-8030-F6LBXVM1-WMH-BTR86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-WMH-BTR86
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1047.0 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365999

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-WMH-BTR86

Luminous Intensity Polar Plot





TEST NUMBER: P365999

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-WMH-BTR86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108248
5°	106469
10°	101447
15°	92697
20°	79496
25°	63788
30°	44721
35°	20664
40°	6636
45°	2137
50°	991
55°	874
60°	874
65°	796
70°	796
75°	913
80°	1155
85°	1890



TEST NUMBER: P365999

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-WMH-BTR86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.9	13.3
10°-20°	346.1	33.1
20°-30°	363.4	34.7
30°-40°	161.3	15.4
40°-50°	20.8	2.0
50°-60°	6.5	0.6
60°-70°	4.6	0.4
70°-80°	3.4	0.3
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	848.4	81.0
0°-40°	1009.7	96.4
0°-60°	1037.0	99.0
0°-90°	1047.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1047.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1512	
5°	1481	139
15°	1250	346
25°	807	363
35°	236	161
45°	21	21
55°	7	7
65°	5	5
75°	3	3
85°	2	2
90°	0	



TEST NUMBER: P365999

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-WMH-BTR86

CANDELA DISTRIBUTION (FULL):

0°	
0°	1511.8
2.5°	1502.4
5°	1481.3
7.5°	1452.6
10°	1395.3
12.5°	1330.9
15°	1250.5
17.5°	1154.2
20°	1043.3
22.5°	926.7
25°	807.4
27.5°	673.4
30°	540.9
32.5°	397.6
35°	236.4
37.5°	125.9
40°	71.0
42.5°	39.0
45°	21.1
47.5°	10.8
50°	8.9
52.5°	8.0
55°	7.0
57.5°	6.6
60°	6.1
62.5°	5.2
65°	4.7
67.5°	3.8
70°	3.8
72.5°	3.3
75°	3.3
77.5°	2.8
80°	2.8
82.5°	2.3
85°	2.3
87.5°	1.4
90°	0.0

(END OF REPORT)