

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365938

Luminaire Tested: **FLD6BX10D010-FEU6B12-8040-F6LBXVM1-WMH-BL89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-45)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8040-F6LBXVM1-WMH-BL89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS ACRYLIC, CLEAR 0.125", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1016.0 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365938

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8040-F6LBXVM1-WMH-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P365938

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8040-F6LBXVM1-WMH-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80		86	82	79		84	81	78	77
5	94	86	80	76	92	85	79	76	83	78	75		81	77	74		80	76	74	72
6	89	81	75	71	88	80	74	71	78	74	70		77	73	70		76	72	69	68
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72	68	65	64
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68	64	61	60
9	77	68	62	59	76	68	62	58	67	62	58		66	61	58		65	61	58	57
10	74	65	59	55	73	64	59	55	63	58	55		63	58	55		62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36105
5°	35868
10°	34102
15°	30946
20°	26847
25°	22821
30°	17959
35°	10117
40°	4543
45°	1889
50°	565
55°	157
60°	104
65°	71
70°	56
75°	74
80°	63
85°	0



TEST NUMBER: P365938

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8040-F6LBXVM1-WMH-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	12.0
10°-20°	303.7	29.9
20°-30°	343.9	33.9
30°-40°	197.2	19.4
40°-50°	42.8	4.2
50°-60°	4.2	0.4
60°-70°	1.2	0.1
70°-80°	0.6	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	769.8	75.8
0°-40°	967.0	95.2
0°-60°	1014.1	99.8
0°-90°	1016.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1016.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1322	
5°	1308	122
15°	1094	304
25°	757	344
35°	303	197
45°	49	43
55°	3	4
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P365938

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8040-F6LBXVM1-WMH-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	1321.8
2.5°	1318.1
5°	1308.1
7.5°	1273.6
10°	1229.5
12.5°	1166.6
15°	1094.3
17.5°	1011.4
20°	923.6
22.5°	841.3
25°	757.2
27.5°	668.3
30°	569.4
32.5°	448.6
35°	303.4
37.5°	191.9
40°	127.4
42.5°	81.5
45°	48.9
47.5°	26.7
50°	13.3
52.5°	5.6
55°	3.3
57.5°	2.6
60°	1.9
62.5°	1.5
65°	1.1
67.5°	1.1
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)