

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364574

Luminaire Tested: **FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR82**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR82
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.187", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1089.1 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.07
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364574

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR82

Luminous Intensity Polar Plot





TEST NUMBER: P364574

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR82

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	83	76	71	90	81	75	70	79	74	69	77	72	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	81	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	43	42
10	63	52	45	41	62	52	45	41	51	45	41	50	44	40	49	44	40	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52763
5°	52821
10°	53396
15°	52920
20°	50717
25°	46715
30°	41348
35°	35252
40°	28798
45°	22520
50°	16609
55°	11510
60°	7361
65°	4473
70°	3036
75°	2352
80°	2062
85°	2875



TEST NUMBER: P364574

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR82

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.2	6.4
10°-20°	199.6	18.3
20°-30°	270.1	24.8
30°-40°	251.2	23.1
40°-50°	172.1	15.8
50°-60°	84.8	7.8
60°-70°	28.3	2.6
70°-80°	9.4	0.9
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	539.9	49.6
0°-40°	791.1	72.6
0°-60°	1048.0	96.2
0°-90°	1089.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1089.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	737	
5°	735	70
15°	714	200
25°	591	270
35°	403	251
45°	222	172
55°	92	85
65°	26	28
75°	8	9
85°	4	3
90°	0	



TEST NUMBER: P364574

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR82

CANDELA DISTRIBUTION (FULL):

	0°
0°	736.9
2.5°	735.9
5°	734.9
7.5°	735.9
10°	734.4
12.5°	726.4
15°	713.9
17.5°	691.0
20°	665.6
22.5°	631.7
25°	591.3
27.5°	547.4
30°	500.1
32.5°	452.7
35°	403.3
37.5°	354.5
40°	308.1
42.5°	263.2
45°	222.4
47.5°	183.5
50°	149.1
52.5°	119.2
55°	92.2
57.5°	70.3
60°	51.4
62.5°	36.9
65°	26.4
67.5°	18.9
70°	14.5
72.5°	11.0
75°	8.5
77.5°	6.5
80°	5.0
82.5°	4.0
85°	3.5
87.5°	2.0
90°	0.0

(END OF REPORT)