

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364581

Luminaire Tested: **FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR94**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364581
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-27)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR94
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM GLASS, TEMPERED CLEAR 0.187", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1152.0 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364581

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR94

Luminous Intensity Polar Plot





TEST NUMBER: P364581

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR94

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	88
3	104	98	93	90	102	96	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		77	74	71	70
7	87	78	73	69	85	77	72	68	76	72	68		75	71	68		74	70	67	66
8	83	74	69	65	82	74	68	65	73	68	64		72	67	64		71	67	64	63
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		67	64	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128948
5°	125530
10°	116032
15°	103297
20°	86994
25°	69326
30°	48557
35°	20568
40°	7178
45°	1964
50°	1003
55°	936
60°	931
65°	847
70°	837
75°	1107
80°	1443
85°	2054



TEST NUMBER: P364581

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR94

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.9	14.1
10°-20°	385.2	33.4
20°-30°	396.3	34.4
30°-40°	169.2	14.7
40°-50°	21.1	1.8
50°-60°	6.8	0.6
60°-70°	5.0	0.4
70°-80°	4.0	0.3
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	943.5	81.9
0°-40°	1112.7	96.6
0°-60°	1140.6	99.0
0°-90°	1152.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1152.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1801	
5°	1746	162
15°	1394	385
25°	878	396
35°	235	169
45°	19	21
55°	8	7
65°	5	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P364581

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR94

CANDELA DISTRIBUTION (FULL):

	0°
0°	1800.9
2.5°	1786.4
5°	1746.5
7.5°	1682.7
10°	1595.9
12.5°	1499.2
15°	1393.5
17.5°	1267.9
20°	1141.7
22.5°	1012.1
25°	877.5
27.5°	735.4
30°	587.3
32.5°	417.3
35°	235.3
37.5°	134.6
40°	76.8
42.5°	39.9
45°	19.4
47.5°	10.5
50°	9.0
52.5°	8.0
55°	7.5
57.5°	7.0
60°	6.5
62.5°	5.5
65°	5.0
67.5°	4.5
70°	4.0
72.5°	4.0
75°	4.0
77.5°	3.5
80°	3.5
82.5°	3.0
85°	2.5
87.5°	1.5
90°	0.0

(END OF REPORT)