

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366009

Luminaire Tested: **FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BL89AM**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-48)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BL89AM
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, OPAL SMOOTH 0.125", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 556.0 lumens
Efficiency: N/A
Efficacy: 39.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.38
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366009

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P366009

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75	82	78	74	79	75	72	70
3	90	80	71	65	88	78	70	64	75	69	63	72	67	62	70	65	61	59
4	83	70	62	55	80	69	61	55	67	59	54	64	58	53	62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46	58	51	46	56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41	52	45	40	51	45	40	38
7	65	51	42	36	63	50	42	36	49	41	36	47	41	36	46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29	40	33	29	39	33	29	27
10	53	40	32	26	52	39	31	26	38	31	26	37	31	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5351
5°	5358
10°	5337
15°	5299
20°	5276
25°	5244
30°	5204
35°	5152
40°	5120
45°	5064
50°	4980
55°	4891
60°	4736
65°	4544
70°	4217
75°	3736
80°	2973
85°	1724



TEST NUMBER: P366009

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.6	3.3
10°-20°	53.0	9.5
20°-30°	80.2	14.4
30°-40°	96.9	17.4
40°-50°	101.0	18.2
50°-60°	91.6	16.5
60°-70°	69.4	12.5
70°-80°	37.6	6.8
80°-90°	7.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	151.8	27.3
0°-40°	248.7	44.7
0°-60°	441.3	79.4
0°-90°	556.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	556.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	196	
5°	195	19
15°	187	53
25°	174	80
35°	154	97
45°	131	101
55°	103	92
65°	70	69
75°	35	38
85°	6	8
90°	0	



TEST NUMBER: P366009

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BL89AM

CANDELA DISTRIBUTION (FULL):

0°	
0°	195.9
2.5°	195.4
5°	195.4
7.5°	194.4
10°	192.4
12.5°	190.4
15°	187.4
17.5°	185.5
20°	181.5
22.5°	178.0
25°	174.0
27.5°	170.0
30°	165.0
32.5°	160.5
35°	154.5
37.5°	149.1
40°	143.6
42.5°	137.6
45°	131.1
47.5°	124.1
50°	117.2
52.5°	110.2
55°	102.7
57.5°	94.7
60°	86.7
62.5°	78.8
65°	70.3
67.5°	61.8
70°	52.8
72.5°	44.4
75°	35.4
77.5°	26.9
80°	18.9
82.5°	12.0
85°	5.5
87.5°	1.5
90°	0.0

(END OF REPORT)