

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364513

Luminaire Tested: **FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL86
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 990.0 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364513

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P364513

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38088
5°	37365
10°	34507
15°	30748
20°	26260
25°	22053
30°	17313
35°	8970
40°	4286
45°	1688
50°	442
55°	124
60°	82
65°	71
70°	56
75°	74
80°	63
85°	125



TEST NUMBER: P364513

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.4	12.8
10°-20°	302.2	30.5
20°-30°	333.6	33.7
30°-40°	183.6	18.5
40°-50°	38.8	3.9
50°-60°	3.3	0.3
60°-70°	1.0	0.1
70°-80°	0.7	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.2	77.0
0°-40°	945.8	95.5
0°-60°	987.9	99.8
0°-90°	990.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	990.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1394	
5°	1363	126
15°	1087	302
25°	732	334
35°	269	184
45°	44	39
55°	3	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P364513

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL86

CANDELA DISTRIBUTION (FULL):

0°	
0°	1394.4
2.5°	1393.7
5°	1362.7
7.5°	1315.0
10°	1244.1
12.5°	1173.5
15°	1087.3
17.5°	999.6
20°	903.4
22.5°	819.0
25°	731.7
27.5°	647.4
30°	548.9
32.5°	419.0
35°	269.0
37.5°	181.3
40°	120.2
42.5°	75.0
45°	43.7
47.5°	22.4
50°	10.4
52.5°	4.5
55°	2.6
57.5°	1.9
60°	1.5
62.5°	1.1
65°	1.1
67.5°	0.7
70°	0.7
72.5°	1.1
75°	0.7
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)