

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364516

Luminaire Tested: **FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364516
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-41)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS ACRYLIC, CLEAR 0.125", 1000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1058.1 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364516

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P364516

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	81	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	59	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40962
5°	40131
10°	37048
15°	32931
20°	28106
25°	23548
30°	18455
35°	9730
40°	4546
45°	1789
50°	467
55°	129
60°	82
65°	71
70°	64
75°	84
80°	63
85°	125



TEST NUMBER: P364516

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	12.8
10°-20°	323.4	30.6
20°-30°	355.7	33.6
30°-40°	196.4	18.6
40°-50°	41.4	3.9
50°-60°	3.4	0.3
60°-70°	1.0	0.1
70°-80°	0.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.6	77.0
0°-40°	1011.0	95.5
0°-60°	1055.8	99.8
0°-90°	1058.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1058.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1500	
5°	1464	135
15°	1164	323
25°	781	356
35°	292	196
45°	46	41
55°	3	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P364516

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	1499.6
2.5°	1488.2
5°	1463.6
7.5°	1407.8
10°	1335.7
12.5°	1253.0
15°	1164.5
17.5°	1069.7
20°	966.9
22.5°	873.5
25°	781.3
27.5°	687.6
30°	585.1
32.5°	445.5
35°	291.8
37.5°	193.9
40°	127.5
42.5°	80.4
45°	46.3
47.5°	24.3
50°	11.0
52.5°	4.6
55°	2.7
57.5°	1.9
60°	1.5
62.5°	1.1
65°	1.1
67.5°	0.8
70°	0.8
72.5°	1.1
75°	0.8
77.5°	0.8
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)