

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364525

Luminaire Tested: **FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364525  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 1000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 832.0 lumens  
Efficiency: N/A  
Efficacy: 83.2 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364525

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI

### Luminous Intensity Polar Plot





TEST NUMBER: P364525

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	64	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93226
5°	91059
10°	83692
15°	74484
20°	63091
25°	50167
30°	35271
35°	14720
40°	5085
45°	1316
50°	668
55°	612
60°	601
65°	593
70°	586
75°	775
80°	866
85°	1479



TEST NUMBER: P364525

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.3	14.1
10°-20°	278.3	33.5
20°-30°	287.2	34.5
30°-40°	122.2	14.7
40°-50°	14.7	1.8
50°-60°	4.4	0.5
60°-70°	3.5	0.4
70°-80°	2.8	0.3
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.8	82.1
0°-40°	805.0	96.7
0°-60°	824.1	99.0
0°-90°	832.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	832.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1302	
5°	1267	117
15°	1005	278
25°	635	287
35°	168	122
45°	13	15
55°	5	4
65°	4	3
75°	3	3
85°	2	2
90°	0	



TEST NUMBER: P364525

CATALOG NUMBER: FLD6BX10D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1302.0
2.5°	1293.6
5°	1266.9
7.5°	1220.6
10°	1151.1
12.5°	1082.7
15°	1004.8
17.5°	917.1
20°	828.0
22.5°	735.0
25°	635.0
27.5°	531.9
30°	426.6
32.5°	302.4
35°	168.4
37.5°	96.8
40°	54.4
42.5°	28.1
45°	13.0
47.5°	7.0
50°	6.0
52.5°	5.3
55°	4.9
57.5°	4.6
60°	4.2
62.5°	3.9
65°	3.5
67.5°	3.2
70°	2.8
72.5°	2.8
75°	2.8
77.5°	2.5
80°	2.1
82.5°	2.1
85°	1.8
87.5°	1.1
90°	0.0

(END OF REPORT)