

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366012

Luminaire Tested: **FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366012  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM ACRYLIC, PATTERN 12 0.125", 1500LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1130.0 lumens  
Efficiency: N/A  
Efficacy: 79.6 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366012

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80

### Luminous Intensity Polar Plot





TEST NUMBER: P366012

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	100	92	86	82	97	91	85	81	88	84	80	85	82	79	83	80	77	76
4	94	85	79	74	92	84	78	73	82	77	72	79	75	72	78	74	71	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	79	68	61	57	77	67	61	57	66	60	56	65	60	56	64	59	56	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47
10	67	56	50	46	66	56	50	46	55	49	45	54	49	45	53	49	45	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	80538
5°	78869
10°	74568
15°	68153
20°	59868
25°	50894
30°	41637
35°	32770
40°	24424
45°	17316
50°	12220
55°	8776
60°	6287
65°	4558
70°	3559
75°	2905
80°	2474
85°	2465



TEST NUMBER: P366012

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.5	9.1
10°-20°	255.8	22.6
20°-30°	294.3	26.0
30°-40°	234.8	20.8
40°-50°	135.4	12.0
50°-60°	64.5	5.7
60°-70°	27.9	2.5
70°-80°	11.5	1.0
80°-90°	3.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	652.6	57.7
0°-40°	887.4	78.5
0°-60°	1087.3	96.2
0°-90°	1130.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1130.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1125	
5°	1097	102
15°	919	256
25°	644	294
35°	375	235
45°	171	135
55°	70	65
65°	27	28
75°	10	11
85°	3	3
90°	0	



TEST NUMBER: P366012

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR80

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1124.8
2.5°	1117.8
5°	1097.3
7.5°	1066.9
10°	1025.6
12.5°	977.2
15°	919.4
17.5°	856.5
20°	785.7
22.5°	714.4
25°	644.2
27.5°	572.9
30°	503.6
32.5°	440.2
35°	374.9
37.5°	316.6
40°	261.3
42.5°	213.9
45°	171.0
47.5°	137.1
50°	109.7
52.5°	87.7
55°	70.3
57.5°	55.3
60°	43.9
62.5°	34.4
65°	26.9
67.5°	21.4
70°	17.0
72.5°	13.5
75°	10.5
77.5°	8.0
80°	6.0
82.5°	4.5
85°	3.0
87.5°	2.0
90°	0.0

(END OF REPORT)