

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366015

Luminaire Tested: **FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366015  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 1500LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1110.1 lumens  
Efficiency: N/A  
Efficacy: 78.2 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366015

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR84

### Luminous Intensity Polar Plot





TEST NUMBER: P366015

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114763
5°	112873
10°	107547
15°	98278
20°	84282
25°	67619
30°	47416
35°	21905
40°	7029
45°	2268
50°	1058
55°	936
60°	931
65°	847
70°	837
75°	968
80°	1237
85°	2054



TEST NUMBER: P366015

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.3	13.3
10°-20°	366.9	33.0
20°-30°	385.3	34.7
30°-40°	171.0	15.4
40°-50°	22.1	2.0
50°-60°	6.9	0.6
60°-70°	4.9	0.4
70°-80°	3.6	0.3
80°-90°	2.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	899.5	81.0
0°-40°	1070.4	96.4
0°-60°	1099.5	99.0
0°-90°	1110.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1110.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1603	
5°	1570	147
15°	1326	367
25°	856	385
35°	251	171
45°	22	22
55°	8	7
65°	5	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P366015

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-WMH-BTR84

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1602.8
2.5°	1592.8
5°	1570.4
7.5°	1540.0
10°	1479.2
12.5°	1411.0
15°	1325.8
17.5°	1223.6
20°	1106.1
22.5°	982.5
25°	855.9
27.5°	714.0
30°	573.5
32.5°	421.5
35°	250.6
37.5°	133.5
40°	75.2
42.5°	41.4
45°	22.4
47.5°	11.5
50°	9.5
52.5°	8.5
55°	7.5
57.5°	7.0
60°	6.5
62.5°	5.5
65°	5.0
67.5°	4.0
70°	4.0
72.5°	3.5
75°	3.5
77.5°	3.0
80°	3.0
82.5°	2.5
85°	2.5
87.5°	1.5
90°	0.0

(END OF REPORT)